



Product Overview

ESDR7534: Transient Voltage Suppressor with 4 lines in SC88 Package

For complete documentation, see the data sheet

Product Description

The ESDR7534 transient voltage suppressor is designed to protect high speed data lines from ESD, EFT, and lightning.

Features

- Protection for IEC61000-4-2 Level4 +/-8kV Contact; +/-15kV Air

Part Electrical Specifications

| Product | Compliance | Status | Dir | V _(BR) Typ (V) | P _{PK} Max (W) | V _{RWM} Max (V) | I _R Max (uA) | V _C Max (V) | Package Type |
|---------------|------------------------|--------|----------------|---------------------------|-------------------------|--------------------------|-------------------------|------------------------|-------------------------------|
| ESDR7534W1T2G | Pb-free Halide free | Active | Unidirectional | 8 | 300 | 5 | 3 | 30 | SC-88-6 / SC-70-6 / SOT-363-6 |

For more information please contact your local sales support at www.onsemi.com

Created on: 7/11/2015