






## SIDELOOKER OPTOLOGIC 4.44x5.08x2.54, 1.90P


CASE 100CM ISSUE A

**DATE 05 MAR 2024** 









## NOTES:

- 1. DIMENSIONING AND TOLERANCING AS PER ASMEY14.5M, 2018.
- 2. CONTROLLING DIMENSION: MILLIMETERS.

DIMENSION (MILLIMETERS)				
	MIN	NOM	MAX	
А	2.41	2.54	2.67	
A1	0.38	0.51	0.64	
A2	0.48	0.53	0.58	
А3	0.64	0.76	0.89	
b	0.51	0.57	0.61	
С	0.51	0.57	0.61	
D	4.32	4.44	4.57	
D1	2.16	2.21	2.29	
D2	2.29	2.41	2.54	
D3	1.78	1.91	2.03	
E	4.83	5.08	5.33	
E1	1.14	1.27	1.40	
е	1.65	1.90	2.15	
øD	1.52	1.65	1.78	
L	12.70	13.46		
L1	1.27	1.52	1.78	
L2	2.29	2.54	2.79	

DOCUMENT NUMBER:	98AON13425G	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.		
DESCRIPTION:	SIDELOOKER OPTOLOGIC	C 4.44x5.08x2.54, 1.90P	PAGE 1 OF 1	

onsemi and ONSEMI are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. onsemi does not convey any license under its patent rights nor the rights of others.