




SOIC-28, 300 mils CASE 751BM-01 ISSUE O

DATE 19 DEC 2008



SYMBOL	MIN	NOM	MAX
A	2.35		2.65
A1	0.10		0.30
A2	2.05		2.55
b	0.31		0.51
с	0.20		0.33
D	17.78		18.03
E	10.11		10.51
E1	7.34		7.60
е		1.27 BSC	
h	0.25		0.75
L	0.40		1.27
θ	0°		8°
θ1	5°		15°





SIDE VIEW

END VIEW

Notes:

All dimensions are in millimeters. Angles in degrees.
Complies with JEDEC MS-013.

DOCUMENT NUMBER:	98AON34296E	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.		
DESCRIPTION:	SOIC-28, 300 MILS		PAGE 1 OF 1	
ON Semiconductor reserves the right the suitability of its products for any pa	to make changes without further notice to an articular purpose, nor does ON Semiconducto	stries, LLC dba ON Semiconductor or its subsidiaries in the United States y products herein. ON Semiconductor makes no warranty, representation r assume any liability arising out of the application or use of any product or icidental damages. ON Semiconductor does not convey any license under	or guarantee regarding circuit, and specifically	