-5.50 MAX--3.70 MAX-

2.90 MAX



WQFN24 4.5x3.5, 0.5P CASE 510CE ISSUE O

DATE 31 AUG 2016

2.00

MAX

2.70

MAX


4.50 MAX


XXXXX


 \bowtie

 \otimes

-0.24 MAX







3.50

BOTTOM VIEW

NOTES:

XXXX

 \boxtimes

0.50 TYP

0.50 TYP

(0.90)

A. CONFORMS TO JEDEC REGISTRATION MO-220, VARIATION WFSD-2 FOR DIMENSIONS ONLY. PIN NUMBERING DOES NOT COMPLY.

RECOMMENDED LAND PATTERN

B. DIMENSIONS ARE IN MILLIMETERS.

C. DIMENSIONS AND TOLERANCES PER ASME Y14.5M, 1994

| DOCUMENT NUMBER: | 98AON13646G | Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red. | |
|------------------|----------------------|---|-------------|
| DESCRIPTION: | WQFN24 4.5X3.5, 0.5P | | PAGE 1 OF 1 |

0.18 - 0.30

0.10M|C|A|B

onsemi and ONSEMI are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. onsemi does not convey any license under its patent rights nor the rights of others.

0.50