

## Product Overview

### DF10S: 1.5A Bridge Rectifier

For complete documentation, see the data sheet.

DF10S

### Features

- Surge overload rating: 50 amperes peak.
- Glass passivated junction.
- Low leakage.
- Lead Free compliant to EU RoHS 2002/95/EU Directives
- Green Molding Compound: IEC61249
- Qualified with IR Reflow and Wave Soldering
- UL Certified, UL #E258596

### Applications

- This product is general usage and suitable for many different applications.

### Part Electrical Specifications

Product	Compliance	Status	Type	$I_{Q(rec)}$ Max (A)	$t_{rr}$ Max (ns)	$V_{RRM}$ Max (V)	$V_{FM}$ Max (V)	$I_{FSM}$ Max (A)	$I_R$ Max (mA)	Package Type
DF10S	Pb-free	Active	Bridge	-	-	1000	1.1	50	0.005	PDIP-4 GW

For more information please contact your local sales support at [www.onsemi.com](http://www.onsemi.com).

Created on: 1/21/2019