

## Product Overview

### MMBT4126LT1: PNP Bipolar Transistor

For complete documentation, see the data sheet.

PNP Silicon

#### Features

- Moisture Sensitivity Level: 1
- ESD Rating--Human Body Model: >4000 V; Machine Model: >400 V
- Pb-Free Package is Available

#### Part Electrical Specifications

Product	Compliance	Status	Polarity	Type	$V_{CE(sat)}$ Max (V)	$I_C$ Cont. (A)	$V_{CEO}$ Min (V)	$V_{CBO}$ (V)	$V_{EBO}$ (V)	$V_{BE(sat)}$ (V)	$V_{BE(on)}$ (V)	$h_{FE}$ Min	$h_{FE}$ Max	$f_T$ Min (MHz)	$P_{TM}$ Max (W)	Package Type
MMBT4126LT1G	Pb-free	Active	PNP	General Purpose	0.4	0.2	25	25	4	0.95	-	120	300	250	0.225	SOT-23-3
	Halide free															
MMBT4126LT3G	Pb-free	Active	PNP	General Purpose	0.4	0.2	25	25	4	0.95	-	120	300	250	0.225	SOT-23-3
	Halide free															

For more information please contact your local sales support at [www.onsemi.com](http://www.onsemi.com).

Created on: 11/17/2018