Surface Mount Schottky Power Rectifier

POWERMITE®
Power Surface Mount Package

MBRM120ET1G, NRVBM120ET1G, MBRM120ET3G, NRVBM120ET3G

The Schottky POWERMITE® employs the Schottky Barrier principle with a barrier metal and epitaxial construction that produces optimal forward voltage drop−reverse current tradeoff. The advanced packaging techniques provide for a highly efficient micro miniature, space saving surface mount Rectifier. With its unique heatsink design, the POWERMITE® has the same thermal performance as the SMA while being 50% smaller in footprint area, and delivering one of the lowest height profiles, < 1.1 mm in the industry. Because of its small size, it is ideal for use in portable and battery powered products such as cellular and cordless phones, chargers, notebook computers, printers, PDAs and PCMCIA cards. Typical applications are AC−DC and DC−DC converters, reverse battery protection, and "Oring" of multiple supply voltages and any other application where performance and size are critical.

Features

- Low Profile − Maximum Height of 1.1 mm
- Small Footprint − Footprint Area of 8.45 mm2
- Low V_F Provides Higher Efficiency and Extends Battery Life
- ESD Ratings:
  - Machine Model = C (> 400 V)
  - Human Body Model = 3B (> 16,000 V)
- Supplied in 12 mm Tape and Reel
- Low Thermal Resistance with Direct Thermal Path of Die on Exposed Cathode Heat Sink
- AEC−Q101 Qualified and PPAP Capable
- NRVB Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements
- All Packages are Pb−Free*

Mechanical Characteristics

- POWERMITE® is JEDEC Registered as DO−216AA
- Case: Molded Epoxy
- Epoxy Meets UL 94 V−0 @ 0.125 in
- Weight: 16.3 mg (approximately)
- Lead and Mounting Surface Temperature for Soldering Purposes 260°C Maximum for 10 Seconds

*For additional information on our Pb−Free strategy and soldering details, please download the **onsemi** Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

SCHOTTKY BARRIER RECTIFIER 1.0 AMPERES, 20 VOLTS



POWERMITE
CASE 457
STYLE 1

MARKING DIAGRAM



BCV = Device Code
M = Date Code
▪ = Pb−Free Package

ORDERING INFORMATION

Device	Package	Shipping†
MBRM120ET1G	POWERMITE (Pb−Free)	3,000 / Tape & Reel
NRVBM120ET1G	POWERMITE (Pb−Free)	3,000 / Tape & Reel
MBRM120ET3G	POWERMITE (Pb−Free)	12,000 / Tape & Reel

DISCONTINUED (Note 1)

NRVBM120ET3G	POWERMITE (Pb−Free)	12,000 / Tape & Reel

†For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specification Brochure, BRD8011/D.

1. **DISCONTINUED:** These devices are not recommended for new design. Please contact your **onsemi** representative for information. The most current information on these devices may be available on www.onsemi.com.

© Semiconductor Components Industries, LLC, 2012

MAXIMUM RATINGS

Symbol	Rating	Value	Unit
V_{RRM} V_{RWM} V_R	Peak Repetitive Reverse Voltage Working Peak Reverse Voltage DC Blocking Voltage	20	V
I_O	Average Rectified Forward Current (At Rated V_R, T_C = 130°C)	1.0	A
I_{FRM}	Peak Repetitive Forward Current (At Rated V_R, Square Wave, 20 kHz, T_C = 135°C)	2.0	A
I_{FSM}	Non−Repetitive Peak Surge Current (Non−Repetitive peak surge current, halfwave, single phase, 60 Hz)	50	A
T_{stg}	Storage Temperature	−65 to 150	°C
T_J	Operating Junction Temperature	−65 to 150	°C
dv/dt	Voltage Rate of Change (Rated V_R, T_J = 25°C)	10,000	V/μs

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

THERMAL CHARACTERISTICS

Symbol	Characteristic	Value	Unit
R_{tjl} R_{tjtab} R_{tja}	Thermal Resistance − Junction−to−Lead (Anode) (Note 1) Thermal Resistance − Junction−to−Tab (Cathode) (Note 1) Thermal Resistance − Junction−to−Ambient (Note 1)	35 23 277	°C/W

1. Mounted with minimum recommended pad size, PC Board FR4, See Figures 9 and 10.

ELECTRICAL CHARACTERISTICS

Symbol	Characteristic	Value		Unit
V_F	Maximum Instantaneous Forward Voltage (Note 2), See Figure 2	**T_J = 25°C**	**T_J = 100°C**	V
	(I_F = 0.1 A) (I_F = 1.0 A) (I_F = 2.0 A)	0.455 0.530 0.595	0.360 0.455 0.540	
I_R	Maximum Instantaneous Reverse Current (Note 2), See Figure 4	**T_J = 25°C**	**T_J = 100°C**	μA
	(V_R = 20 V) (V_R = 10 V) (V_R = 5.0 V)	10 1.0 0.5	1600 500 300	

2. Pulse Test: Pulse Width ≤ 250 μs, Duty Cycle ≤ 2%.

Share Feedback
Your Opinion Matters



Figure 1. Typical Forward Voltage



Figure 2. Maximum Forward Voltage



Figure 3. Typical Reverse Current



Figure 4. Maximum Reverse Current



Figure 5. Current Derating



Figure 6. Forward Power Dissipation

Share Feedback
Your Opinion Matters



Figure 7. Capacitance



Figure 8. Typical Operating Temperature Derating*

* Reverse power dissipation and the possibility of thermal runaway must be considered when operating this device under any reverse voltage conditions. Calculations of T_J therefore must include forward and reverse power effects. The allowable operating T_J may be calculated from the equation: $T_J = T_{Jmax} - r(t)(Pf + Pr)$ where

r(t) = thermal impedance under given conditions,
Pf = forward power dissipation, and
Pr = reverse power dissipation

This graph displays the derated allowable T_J due to reverse bias under DC conditions only and is calculated as $T_J = T_{Jmax} - r(t)Pr$, where r(t) = Rthja. For other power applications further calculations must be performed.

Share Feedback
Your Opinion Matters



Figure 9. Thermal Response Junction to Lead



Figure 10. Thermal Response Junction to Ambient

POWERMITE is a registered trademarks of and used under a license from Microsemi Corporation.

Share Feedback
Your Opinion Matters

POWERMITE 1.90x1.96x1.00
CASE 457
ISSUE H

DATE 16 MAY 2025



TOP VIEW



SIDE VIEW



BOTTOM VIEW



RECOMMENDED MOUNTING FOOTPRINT

*For additional information on our Pb−Free Strategy and Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

MILLIMETERS			
DIM	MIN	NOM	MAX
A	0.85	1.00	1.15
A1	0.00	0.05	0.10
b	0.40	0.55	0.69
b1	0.70	0.85	1.00
c	0.10	0.18	0.25
D	1.75	1.90	2.05
E	1.75	1.96	2.18
H	3.60	3.75	3.90
L	1.20	1.35	1.50
L1	0.50	0.65	0.80
L2	0.50 REF		

NOTES:
1. DIMENSIONING AND TOLERANCING AS PER ASME Y14.5M, 2018.
2. CONTROLLING DIMENSION: MILLIMETERS.
3. DIMENSION D & E DO NOT INCLUDE MOLD FLASH, PROTRUSIONS OR GATE BURRS.

GENERIC MARKING DIAGRAMS*



STYLE 1 **STYLE 2**



STYLE 3

XXX = Specific Device Code
M = Date Code
▪ = Pb−Free Package

STYLE 1:
PIN 1. CATHODE
2. ANODE

STYLE 2:
PIN 1. ANODE OR CATHODE
2. CATHODE OR ANODE
(BI−DIRECTIONAL)

STYLE 3:
PIN 1. ANODE
2. CATHODE

*This information is generic. Please refer to device data sheet for actual part marking. Pb−Free indicator, “G” or microdot “▪”, may or may not be present. Some products may not follow the Generic Marking.

DOCUMENT NUMBER:	**98ASB14853C**	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped “CONTROLLED COPY” in red.	
DESCRIPTION:	**POWERMITE 1.90x1.96x1.00**		**PAGE 1 OF 1**

onsemi and onsemi are trademarks of Semiconductor Components Industries, LLC dba **onsemi** or its subsidiaries in the United States and/or other countries. **onsemi** reserves the right to make changes without further notice to any products herein. **onsemi** makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. **onsemi** does not convey any license under its patent rights nor the rights of others.

onsemi, ONSEMI , and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent−Marking.pdf. **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as−is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:
Technical Library: www.onsemi.com/design/resources/technical−documentation
onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support
For additional information, please contact your local Sales Representative at
www.onsemi.com/support/sales