

ON Semiconductor

Is Now

onsemi™

To learn more about onsemi™, please visit our website at
www.onsemi.com

onsemi and **onsemi** and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi** product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner. Other names and brands may be claimed as the property of others.

NCP457xx Evaluation Board User's Manual

Introduction

This user's manual provides detailed information regarding the configuration and use of the NCP457xx evaluation boards. Each NCP457xx product has a different pin out, however, the external connections to the evaluation boards are the same. This manual focuses on the evaluations boards' common external connections and use.

Evaluation Board Features

- 1 NCP457xx part
- High Current Connection for Load Switch V_{IN} .
- High Current Connection for Load Switch V_{OUT} .
- Jumpers for connecting Power Good pull up resistor.
- Jumper for connecting a capacitor to externally program the slew rate.
- Jumper for connecting a resistor to ground for OCP programming.

Quick Start

Recommended Equipment

Before beginning, the following equipment is needed:

- 2 DC power supplies (1 capable of at least 24V, and 1 capable of at least 5V).
- 1 DC load (can be active or passive)
- Function generator or DC supply to drive the EN signal
- Oscilloscope (for observation of signals)
- Digital Multi-meter (for observation of signals)
- Banana cables for V_{IN} / V_{OUT} / V_{CC} / GND connections

Board Setup

The table below describes the voltages or currents intended for each connection on the evaluation board.

Connection	Voltage / Current	Notes
V_{IN}	0V – 24V	
V_{OUT}	0A – I_{max}	OCP setting affects possible load currents.
V_{CC}	3V – 5.5V	Controller supply
GND	0V	
J1	Install for max OCP setting.	OCP programming connection.
J2	Remove to for fastest slew rate setting.	SR programming connection.
J3	Connect if using the PG signal	Connects a 100k Ω pull-up resistor to VCC PG pin



ON Semiconductor®

<http://onsemi.com>

Testing Procedure

The NCP457xx EVK comes fully assembled and tested. Follow the steps below to verify board operation. Refer to the schematic and layout diagrams found on the ON Semiconductor website for specific device connections.

- 1) Ensure Jumper connection are correct for desired SR, OCP, and PG settings.
- 2) Apply DC power to the V_{IN} input (2V - 24V).
- 3) Apply DC power to V_{CC} (3V – 5.5V).
- 4) Apply 0.5A load current connected to V_{OUT} .

(Steps 2, 3, and 4 can occur in any order).

- 5) Enable load switch by asserting the EN signal.
- 6) Measure V_{OUT} using test loop. V_{OUT} should be within 20mV of V_{IN} . This difference depends on the specific R_{ON} of the part under test plus board resistance from the measurement point to the device.
- 7) Disable the device by asserting EN low. Measure V_{OUT} . It should measure 0V.

The PG signal should go high and low with the enabling and disabling of the device if J3 is connected. Attaching an oscilloscope to V_{OUT} will allow for observation of the soft start change as J2 is connected or disconnected. This board can be used to evaluate all fault conditions as defined in the specific datasheets.