

Test Procedure for the NCV890204MWGEVB Evaluation Board

OPERATIONAL GUIDELINES

- 1. Connect a dc input voltage, within the 6.0 V to 36 V range, between VIN and GND.
- 2. Connect a dc enable voltage, within the $2.0\ V$ to $36\ V$ range, between EN and GND. This will power up the switcher. The VOUT signal should be $3.3\ V$.
- 3. Add a load to VOUT up to 2.0 A.

