

FMMT549

PNP Low Saturation Transistor

Product Overview

For complete documentation, see the data sheet.

FMMT549



Features

- This device is designed with high current gain and low saturation voltage with collector currents up to 2A continuous.
- Sourced from process PB

Applications

- This product is general usage and suitable for many different applications.

Part Electrical Specifications

Product	Pricing (\$/Unit)	Compliance	Status	Polarity	Type	$V_{CE(sat)Max}$ (V)	I_C Cont. (A)	V_{CE0Min} (V)	V_{CBO} (V)	V_{EBO} (V)	$V_{BE(sat)}$ (V)	V_{BE0} (V)	$h_{FE} Min$	$h_{FE} Max$	f_T Min (MHz)	$P_{TM} Max$ (W)	Package Type
FMMT549	0.1025	 	Active	PNP	LOW $V_{CE(sat)}$	0.75	1	30	35	5	1.25	1	100	300	100	0.5	SOT-23-3