

NTD60N02R

Power MOSFET 25V 62A 10.5 mOhm Single N-Channel DPAK

Product Overview

For complete documentation, see the data sheet.

Power MOSFET 62 Amps, 25 Volts, N-channel, DPAK

Features

- Low RDS(on) to Minimize Conduction Loss
- Low Ciss to Minimize Driver Loss
- Low Gate Charge
- Optimized for High Side Switching Requirements in High Efficiency DC-DC Converters
- Pb-Free Packages are Available