

GBU6K

6 A Bridge Rectifier

Product Overview

For complete documentation, see the data sheet.


GBU6K

Features

- Glass-Passivated Junction
- Surge Overload Rating: 175 A peak
- Reliable Low-Cost Construction Utilizing Molded Plastic Technique
- Ideal for Printed Circuit Board
- UL certified, UL #E258596

Applications

- This product is general usage and suitable for many different applications.

Part Electrical Specifications											
Product	Pricing (\$/Unit)	Compliance	Status	Type	$I_{O(rec)}$ Max (A)	t_{rr} Max (ns)	V_{RRM} Max (V)	V_{FM} Max (V)	I_{FSM} Max (A)	I_R Max (mA)	Package Type
GBU6K	0.5783		Active	Bridge	6	-	800	1	175	0.005	SIP-4