

FSV530AF

Schottky Barrier Rectifier

Product Overview

For complete documentation, see the data sheet.

FSV530AF

Features

- Low Forward Voltage Drop: 0.54 V Maximum at 5 A, TA = 25°C
- Ultra Thin Profile - Maximum Height of 1.0 mm
- High Surge Capacity
- UL Flammability 94V-0 Classification
- MSL level 1
- RoHS Compliant / Green Mold Compound