

## SS24FL

# Surface Mount Schottky Barrier Rectifier

## Product Overview

For complete documentation, see the data sheet.

SS24FL

### Features

- Ultra Thin Profile – Maximum Height of 1.08 mm
- UL Flammability 94V-0 Classification
- MSL level 1
- RoHS Compliant / Green Mold Compound

### Part Electrical Specifications

Product	Pricing (\$/Unit)	Compliance	Status	Configuration	$V_{RRM}$ Min (V)	$V_F$ Max (V)	$I_{RM}$ Max ( $\mu$ A)	$I_{O(rec)Max}$ (A)	$I_{FSM}$ Max (A)	$t_{rr}$ Max (ns)	$C_j$ Max (pF)	Package Type
SS24FL	0.0485	 	Active	Single	40	0.55	400	2	50	9.495	-	SOD-123 FL