

Product Overview

FSV330AF: Schottky Barrier Rectifier

For complete documentation, see the data sheet.

FSV330AF

Features

- Low Forward Voltage Drop: 0.5 V Maximum at 3 A, TA = 25°C
- Ultra Thin Profile - Maximum Height of 1.0 mm
- High Surge Capacity
- UL Flammability 94V-0 Classification
- MSL level 1
- RoHS Compliant / Green Mold Compound

Part Electrical Specifications

Product	Pricing (\$/Unit)	Compliance	Status	Configuration	V _{RRM} Min (V)	V _F Max (V)	I _{RM} Max (μA)	I _{O(rec) Max} (A)	I _{FSM} Max (A)	t _{rr} Max (ns)	C _j Max (pF)	Package Type
FSV330AF	0.0972	Pb-free Halide free	Active	Single	30	500	100	3	80	12.5	485	SMA-FL

For more information please contact your local sales support at www.onsemi.com.

Created on: 7/1/2020