

Product Overview

MBR460MFS: Schottky Power Rectifier, Switch-mode, 4.0 A, 60 V

For complete documentation, see the data sheet.

MBR460MFS

Part Electrical Specifications												
Product	Pricing (\$/Unit)	Compliance	Status	Configuration	V_{RRM} Min (V)	V_F Max (V)	I_{RM} Max (μ A)	$I_{O(rec)}$ Max (A)	I_{FSM} Max (A)	t_{rr} Max (ns)	C_j Max (pF)	Package Type
MBR460MFST1G	0.138	Pb-free Halide free	Active	Single	60	0.74	200	4	40	-	-	SO-8FL / DFN-5
MBR460MFST3G	0.138	Pb-free Halide free	Active	Single	60	0.74	200	4	40	-	-	SO-8FL / DFN-5
NRVB460MFST1G	0.1449	AEC Qualified PPAP Capable Pb-free Halide free	Active	Single	60	0.74	200	4	40	-	-	SO-8FL / DFN-5
NRVB460MFST3G	0.1449	AEC Qualified PPAP Capable Pb-free Halide free	Active	Single	60	0.74	200	4	40	-	-	SO-8FL / DFN-5

For more information please contact your local sales support at www.onsemi.com.

Created on: 4/5/2020