

Product Overview

MMSZ15E: 225 W Energy Rated Zener 15 V SOD-123

For complete documentation, see the data sheet.

Three complete series of Zener diodes are offered in the convenient, surface mount plastic SOD-123 package. These devices provide a convenient alternative to the leadless 34-package style.

Features

- Peak Power – 225 Watt (8 X 20 s)
- 500 mW Rating on FR-4 or FR-5 Board
- Small Package Size for High Density Applications
- Pb-Free Packages are Available
- AEC-Q101 Qualified and PPAP Capable
- SZ Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements

Part Electrical Specifications

Product	Pricing (\$/Unit)	Compliance	Status	V _Z Typ (V)	P Max (W)	Package Type
SZMMSZ15ET1G	0.034	AEC Qualified PPAP Capable Pb-free Halide free	Active	15	0.5	SOD-123

For more information please contact your local sales support at www.onsemi.com.

Created on: 11/22/2019