

Product Overview

NGTB10N60FG: IGBT N-Channel, 600V, 10A, VCE(sat)=1.5V, TO-220F-3FS

For complete documentation, see the data sheet.

NGTB10N60FG is N-Channel IGBT, 600V, 10A, VCE(sat)=1.5V, TO-220F-3FS.

Features

- IGBT VCE(sat)=1.5V typ (IC=10A, VGE=15V)
- IGBT IC=20A (Tc=25°C)
- Adaption of full isolation type package
- 5µs short circuit capability
- Diode VF=1.3V typ (IF=10A)
- Diode trr=70ns typ
- Enhancement type

Applications

- Power factor correction of white goods appliance
- General purpose inverter

End Products

- Sewing machine
- Dishwasher
- Refrigerator
- Clothes Washer

Part Electrical Specifications

Product	Compliance	Status	V _{ES} ^{(BR)C} Typ (V)	I _C Max (A)	V _{GE(sat)} Typ (V)	V _F Typ (V)	E _{off} Typ (mJ)	E _{on} Typ (mJ)	T _{rr} Typ (ns)	I _{rr} Typ (A)	Gate Charge Typ (nC)	Short Circuit Withstand (µs)	E _{AS} Typ (mJ)	P _D Max (W)	Co- Pack aged Diode	Package Type
NGTB10N60FG	Pb-free Halide free	Active	600	10	1.5	1.3	-	-	70	-	55	5	-	40	Yes	TO-220-3 Full Pack

For more information please contact your local sales support at www.onsemi.com.

Created on: 9/20/2019