

Product Overview

NTLJD3115P: Dual P-Channel Power MOSFET -20V -4.1A 100mΩ

For complete documentation, see the data sheet.

Power MOSFET -20 V, -4.1 A, μCool™ Dual P-Channel, 2x2 mm WDFN Package

Features

- WDFN Package Provides Exposed Drain Pad for Excellent Thermal Conduction
- 2x2 mm Footprint Same as SC-88
- Lowest RDS(on) Solution in 2x2 mm Package
- 1.8 V RDS(on) Rating for Operation at Low Voltage Gate Drive Logic Level
- Low Profile (< 0.8 mm) for Easy Fit in Thin Environments
- Bidirectional Current Flow with Common Source Configuration

Applications

- Optimized for Battery and Load Management Applications in Portable Equipment
- Li-Ion Battery Charging and Protection Circuits
- High Side Load Switch

For more information please contact your local sales support at www.onsemi.com.

Created on: 7/23/2021

