

FAN49103





Buck-Boost Regulator, 2.5 A, 1.8 MHz, TinyPower™ I2C

Product Overview

For complete documentation, see the data sheet.

FAN49103

Part Electrical Specifications

| Product | Pricing (\$/Unit) | Compliance | Status | Topology | Control Mode | V _{CC} Min (V) | V _{CC} Max (V) | V _O Typ (V) | I _O Typ (A) | Efficiency (%) | f _{SW} Typ (kHz) | Package Type |
|-----------------|-------------------|---|--------|-------------------|--------------|-------------------------|-------------------------|------------------------|------------------------|----------------|---------------------------|--------------|
| FAN49103AUC330X | 0.4336 |   | Active | Step-Up/Step-Down | Current Mode | 2.5 | 5.5 | 3.3 | 2.5 | 96 | 1800 | WLCSP-20 |
| FAN49103AUC340X | 0.4336 |   | Active | Step-Up/Step-Down | Current Mode | 2.5 | 5.5 | 3.4 | 2.5 | 96 | 1800 | WLCSP-20 |