

6

5

4

3


2

1

SIZE	QTY	SYM	PLATED	TOL
0.4	166	+	YES	via
1.1	6	×	YES	+/-0.05
2.4	2	□	YES	+/-0.05

REVISION RECORD			
LTR	ECO NO:	APPROVED:	DATE:

FABRICATION DRAWING



COMPLIANT RoHS DIRECTIVE 2011/65/EU

MATERIAL	FR4 IMPROVED (low CTE)		
BOARD THICKNESS		1.6mm /63mils	
STACKUP	MC6 /6LAYERS		
MINIMAL GAP		150um /6.0mils	
MINIMAL SLIVER		150um /6.0mils	
COPPER THICKNESS		35um(1oz)at START	
FINISH THICKNESS	CHEMICAL NiAu		
SOLDER MASK		GREEN TOP&BOT	
SILKSCREEN	WHITE TOP&BOT		
ALL BOARD ELECTRICALLY TESTED			
MANUFACTURE 'S LOGO & DATECODE MARKED ON BOTTOM SOLDERMASK			

COMPANY:

ON Semiconductor

TITLE:

NCP1565 100W 3.3V Quarter Brick

CODE:

SIZE:

DRAWING NO:

REV:

TLS

B

NCP1565

01.1 |

SCALE: 1/1

SHEET: 3 OF 3

D

D

C

C

B

B

A

A