

# Bipolar Transistor

**-12 V, -1 A, Low  $V_{CE(sat)}$   
 PNP Single MCPH3**

**12A02MH**

### Features

- Large Current Capacity
- Low Collector-To-Emitter Saturation Voltage (Resistance)  
 $R_{CE(sat)}$  typ. = 285 m $\Omega$  [ $I_C = 1$  A,  $I_B = 50$  mA]
- Small ON-Resistance ( $R_{on}$ )
- This Device is Pb-Free

### Applications


- Low-Frequency Amplifier, High-Speed Switching, Small Motor Drive, Muting Circuit

### ABSOLUTE MAXIMUM RATINGS

(Values are at  $T_A = 25^\circ\text{C}$  unless otherwise noted.)


Symbol	Parameter	Conditions	Ratings	Unit
$V_{CBO}$	Collector-Base Voltage		-15	V
$V_{CEO}$	Collector-Emitter Voltage		-12	V
$V_{EBO}$	Emitter-Base Voltage		-5	V
$I_C$	Collector Current		-1	A
$I_{CP}$	Collector Current (Pulse)		-2	A
$P_C$	Collector Dissipation	When mounted on ceramic substrate (600 mm <sup>2</sup> × 0.8 mm)	600	mW
$T_J$	Junction Temperature		150	°C
$T_{STG}$	Storage Temperature Range		-55 to 150	°C

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.




MCPH3  
 CASE 419AQ

### ELECTRICAL CONNECTION



### MARKING DIAGRAM



AK = Device Code

### ORDERING INFORMATION

Device	Package	Shipping <sup>†</sup>
12A02MH-TL-E	MCPH3 (Pb-Free)	3000 / Tape & Reel


<sup>†</sup>For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, [BRD8011/D](http://BRD8011/D).

# 12A02MH

## ELECTRICAL CHARACTERISTICS (Values are at $T_A = 25^\circ\text{C}$ unless otherwise noted.)

Symbol	Parameter	Conditions	Min	Typ	Max	Unit
$I_{CBO}$	Collector Cut-Off Current	$V_{CB} = -12\text{ V}, I_E = 0\text{ A}$	-	-	-100	nA
$I_{EBO}$	Emitter Cut-Off Current	$V_{EB} = -4\text{ V}, I_C = 0\text{ A}$	-	-	-100	nA
$h_{FE}$	DC Current Gain	$V_{CE} = -2\text{ V}, I_C = -10\text{ mA}$	300	-	700	-
$f_T$	Gain-Bandwidth Product	$V_{CE} = -2\text{ V}, I_C = -50\text{ mA}$	-	450	-	MHz
$C_{ob}$	Output Capacitance	$V_{CB} = -10\text{ V}, f = 1\text{ MHz}$	-	6	-	pF
$V_{CE(sat)}$	Collector-Emitter Saturation Voltage	$I_C = -400\text{ mA}, I_B = -20\text{ mA}$	-	-120	-240	mV
$V_{BE(sat)}$	Base-Emitter Saturation Voltage	$I_C = -400\text{ mA}, I_B = -20\text{ mA}$	-	-0.9	-1.2	V
$V_{(BR)CBO}$	Collector-to-Base Breakdown Voltage	$I_C = -10\text{ }\mu\text{A}, I_E = 0\text{ A}$	-15	-	-	V
$V_{(BR)CEO}$	Collector-to-Emitter Breakdown Voltage	$I_C = -1\text{ mA}, R_{BE} = \infty$	-12	-	-	V
$V_{(BR)EBO}$	Emitter-to-Base Breakdown Voltage	$I_E = -10\text{ }\mu\text{A}, I_C = 0\text{ A}$	-5	-	-	V
$t_{on}$	Turn-ON Time	See Figure. 1	-	30	-	ns
$t_{stg}$	Storage Time		-	75	-	ns
$t_f$	Fall Time		-	15	-	ns

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.



$$I_C = 20\text{ mA}, I_{B1} = -20\text{ mA}, I_{B2} = -400\text{ mA}$$

**Figure 1. Switching Time Test Circuit**

TYPICAL CHARACTERISTICS




Figure 2.  $I_C - V_{CE}$




Figure 3.  $I_C - V_{BE}$




Figure 4.  $h_{FE} - I_C$




Figure 5.  $V_{CE(sat)} - I_C$




Figure 6.  $V_{CE(sat)} - I_C$




Figure 7.  $V_{BE(sat)} - I_C$

TYPICAL CHARACTERISTICS (continued)




Figure 9.  $C_{ob} - V_C$




Figure 8.  $f_T - I_C$




Figure 10.  $R_{on} - I_B$





Figure 11.  $P_C - T_A$

**SC-70FL / MCPH3**  
**CASE 419AQ**  
**ISSUE O**

DATE 30 DEC 2011



<b>DOCUMENT NUMBER:</b>	<b>98AON65644E</b>	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.
<b>DESCRIPTION:</b>	<b>SC-70FL / MCPH3</b>	<b>PAGE 1 OF 1</b>

ON Semiconductor and are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. ON Semiconductor does not convey any license under its patent rights nor the rights of others.

**onsemi**, **Onsemi**, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at [www.onsemi.com/site/pdf/Patent-Marking.pdf](http://www.onsemi.com/site/pdf/Patent-Marking.pdf). **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

## ADDITIONAL INFORMATION

### TECHNICAL PUBLICATIONS:

Technical Library: [www.onsemi.com/design/resources/technical-documentation](http://www.onsemi.com/design/resources/technical-documentation)  
onsemi Website: [www.onsemi.com](http://www.onsemi.com)

### ONLINE SUPPORT: [www.onsemi.com/support](http://www.onsemi.com/support)

For additional information, please contact your local Sales Representative at [www.onsemi.com/support/sales](http://www.onsemi.com/support/sales)

