

 <b>Material Composition Declaration</b> © Copyright 2005, IPC, Bannockburn, Illinois. All rights reserved under both international and Pan-American copyright conventions.		This document is a declaration of the substances within the manufacturer listed item. Note: if the item is an assembly with lower level parts, the declaration encompasses all lower level materials for which the manufacturer has engineering responsibility.								
1752-21.1		IPC Web Site for Information on IPC-1752 Standard <a href="http://www.ipc.org/IPC-175x">http://www.ipc.org/IPC-175x</a>			Form Type * Distribute		Declaration Class * Class 6 - RoHS Yes/No, Homogeneous Materials and Mfg Information			
<b>Supplier Information</b>										
<b>Company name*</b> onsemi			Company unique ID			Unique ID Authority		<b>Response Date*</b> 2024-05-01		
<b>Contact Name</b> Product-Env-Stewards			Title - Contact Product Enviro Compliance			<b>Phone - Contact*</b> NA		<b>Email - Contact*</b> Product-Env-Stewards@onsemi.com		
<b>Authorized Representative*</b> Product-Env-Stewards			Title - Representative Product Enviro Compliance			<b>Phone - Representative*</b> NA		<b>Email - Representative*</b> Product-Env-Stewards@onsemi.com		
	Requester Item Number	Mfr Item Number	Mfr Item Name		Effective Date	Version	Manufacturing Site	Weight*	UOM	Unit Type
		MT9P031I12STM-TP	5 MP 1/3 CIS		2024-05-01		TA1	259.0	mg	Each
<b>Manufacturing Process Information</b>										
	Terminal Plating / Grid Array Material	Terminal Base Alloy	J-STD-020 MSL Rating		Peak Process Body Temperature		Max Time at Peak Temperature		Number of Reflow Cycles	
	Precious metal (e.g. Ag,Au, NiPdAu) (no Sn)	CU Alloy	4		260	C	30	seconds	3	
Comments										
For more information regarding material composition please refer to page 3										

RoHS Material Composition Declaration		Declaration Type *	Detailed
Directive 2015/863/EU amending RoHS Directive 2011/65/EU	RoHS Definition: Quantity limit of 0.01% by mass (100 PPM) in homogeneous material for Cadmium and quantity limit of 0.1% by mass (1000 PPM) in homogeneous material for: Lead (Pb), Mercury (Hg), Hexavalent Chromium (Cr6+), Polybrominated Biphenyls (PBB), Polybrominated Diphenyl Ethers (PBDE), and Bis(2-ethylhexyl) phthalate (DEHP), Benzyl-butyl phthalate (BBP), Dibutyl phthalate (DBP), Diisobutyl phthalate (DIBP).		
<p>Please indicate whether any homogeneous material (as defined by the RoHS Directive, EU 2011/65/EU and implemented by the laws of the European Union member states) of the part identified on this form contains lead, mercury, cadmium, hexavalentchromium, polybrominated biphenyls and/or polybrominated diphenyl ethers (each a “RoHS restricted substance”) in excess of the applicable quantity limit identified above. If a homogeneous material within the part contains a RoHS restricted substance in excess of an applicable quantity limit, please indicate below which, if any, RoHS exemption you believe may apply. If the part is an assembly with lower level components, the declaration shall encompass all such components. Supplier certifies that it gathered the information it provides in this form using appropriate methods to ensure its accuracy and that such information is true and correct to the best of its knowledge and belief, as of the date that Supplier completes this form. Supplier acknowledges that Company will rely on this certification in determining the compliance of its products with European Union member state laws that implement the RoHS Directive. Company acknowledges that Supplier may have relied on information provided by others in completing this form, and that Supplier may not have independently verified such information. However, in situations where Supplier has not independently verified information provided by others, Supplier agrees that, at a minimum, its suppliers have provided certifications regarding their contributions to the part, and those certifications are at least as comprehensive as the certification in this paragraph. If the Company and the Supplier enter into a written agreement with respect to the identified part, the terms and conditions of that agreement, including any warranty rights and/or remedies provided as part of that agreement, will be the sole and exclusive source of the Supplier’s liability and the Company’s remedies for issues that arise regarding information the Supplier provides in this form. In the absence of such written agreement, the warranty rights and/or remedies of Supplier's Standard Terms and Conditions of Sale applicable to such part shall apply.</p>			
RoHS Declaration *	1 - Item(s) does not contain RoHS restricted substances per the definition above		Supplier Acceptance * Accepted
<b>Exemption: If the declared item does not contain RoHS restricted substances per the definition above except for defined RoHS exemptions, then select the corresponding response in the RoHS Declaration above and choose all applicable exemptions.</b>			
Exemption List Version	EL-2011/534/EU		
Declaration Signature			
<b>Instructions: Complete all of the required fields on all pages of this form. Select the "Accepted" on the Supplier Acceptance drop-down. This will display the signature area. Digitally sign the declaration (if required by the Requester) and click on Submit Form to have the form returned to the Requester.</b>			
Supplier Digital Signature	Rastislav Drska		

**Homogeneous Material Composition Declaration for Electronic Products**

SubItem Instructions: The presence of any JIG Level A or B substances must be declared. [1] indicate the subpart in which the substance is located, [2] provide a description of the homogeneous material [3], enter the weight of the homogeneous material.

Substance Instructions: [A] select the Level (JIG A, JIG B, Requester or Supplier) [B] select the substance category (JIG or Requester) or enter a value (Supplier). [C] select the substance (JIG) or enter the substance and CAS (Other). [D] select a RoHS exemption, if applicable [E] enter the weight of the substance or the PPM concentration [F] Optionally enter the positive (+) and negative (-) tolerance in percent (Note: percent tolerance values are expected to cover a 3 sigma range of distribution unless otherwise noted).

Homogeneous Material	Weight	Unit of Measure	Level	Substance	CAS	Exempt	Weight	Unit of Measure
Die	59.5	mg		Misc.	proprietary data		0.2261	mg
			Supplier	Silicon (Si)	7440-21-3		58.6848	mg
			Supplier	Aluminum (Al)	7429-90-5		0.589	mg
Die Attach	2.2	mg	Supplier	Bisphenol A_Epichlorohydrin Polymer	25068-38-6		0.825	mg
			Supplier	Ethylene Glycol	107-21-1		0.022	mg
			Supplier	Sulfonium (Thiodi-4,1-phenylene)	89452-37-9		0.066	mg
			Supplier	Modified Silicon Dioxide (SiO2)	67762-90-7		0.462	mg
			Supplier	Formaldehyde Polymer	9003-36-5		0.825	mg
Imaging Lens	55.3	mg	Supplier	Titanium Dioxide (TiO2)	13463-67-7		2.765	mg
			Supplier	Sodium Monoxide (Na2O)	1313-59-3		2.765	mg
			Supplier	Boron Trioxide (B2O3)	1303-86-2		2.765	mg
			Supplier	Zinc Monoxide (ZnO)	1314-13-2		2.765	mg
			B	Antimony Trioxide (Sb2O3)	1309-64-4		0.2765	mg
			Supplier	Aluminum Trioxide (Al2O3)	1344-28-1		2.765	mg
			Supplier	Potassium Monoxide (K2O)	12136-45-7		2.765	mg
			Supplier	Silica Crystalline (SiO2)	14808-60-7		38.4335	mg
Lid Attach	2.4	mg	Supplier	Bisphenol A_Epichlorohydrin Polymer	25068-38-6		0.7584	mg
			Supplier	Filler (SiO2)	68909-20-6		0.1248	mg
			Supplier	Epoxy Prepolymer	Proprietary Data		0.7584	mg
			Supplier	Formaldehyde Polymer	9003-36-5		0.7584	mg
Mold Compound-Black	55.0	mg		Phenolic Resin	proprietary data		8.25	mg
			Supplier	Oxirane	39817-09-9		8.25	mg
			Supplier	1,4-Bis(2,3-epoxypropoxy)butane	2425-79-8		1.65	mg
			Supplier	Carbon Black (C)	1333-86-4		0.55	mg
			Supplier	Fused Silica (SiO2)	60676-86-0		35.2	mg
			Supplier	Silica Crystalline (SiO2)	14808-60-7		1.1	mg
Substrate and Solder Mask	84.3	mg	Supplier	Fiber Glass (SiO2)	65997-17-3		17.8632	mg
			Supplier	Inorganic Filler of Solder Mask_Talc (Mg3Si4O10(OH)2)	14807-96-6		1.1043	mg
			Supplier	Silica Amorphous (SiO2)	7631-86-9		0.2782	mg
			Supplier	Acetophenone Derivative	Proprietary Data		1.6523	mg
			Supplier	Carbon Black (C)	1333-86-4		0.2782	mg

			Supplier	2,4-Diethyl-9H-thioxanthen-9-one (DETX)	82799-44-8		0.2782	mg
			Supplier	Aluminum Hydroxide (Al(OH)3)	21645-51-2		8.194	mg
			Supplier	Solvent Naphtha (Solvent oil)	64742-94-5		3.3046	mg
			Supplier	Bismaleimide Triazine resin	Proprietary Data		2.8325	mg
			Supplier	Copper (Cu)	7440-50-8		39.9666	mg
			Supplier	Barium Sulfate (BaSO4)	7727-43-7		8.548	mg
Wire Bond - Au	0.3	mg	Supplier	Gold (Au)	7440-57-5		0.3	mg