



## Product Overview

### 2SA1705: Bipolar Transistor, -50V, -1A, Low VCE(sat), PNP Single NMP

For complete documentation, see the [data sheet](#)

#### Product Description

2SA1705 is Bipolar Transistor, -50V, -1A, Low VCE(sat), PNP Single NMP for Low-Frequency Power Amplifier Applications.

#### Features

- Adoption of FBET process
- Fast switching speed

#### Applications

- Voltage regulators, Relay drivers, Lamp drivers

#### Part Electrical Specifications

Product	Compliance	Status	Polarity	I <sub>C</sub> Continuous (A)	V <sub>(BR)CEO</sub> Min (V)	h <sub>FE</sub> Min	h <sub>FE</sub> Max	f <sub>T</sub> Min (MHz)	P <sub>TM</sub> Max (W)	Package Type
2SA1705S-AN	Pb-free	Active	PNP	1	50	140	280	150	0.9	NMP (Taping)
2SA1705T-AN	Pb-free	Active	PNP	1	50	200	400	150	0.9	NMP (Taping)

For more information please contact your local sales support at [www.onsemi.com](http://www.onsemi.com)

Created on: 7/11/2015