



Product Overview

2SA1709: Bipolar Transistor, -100V, -2A, Low VCE(sat), (PNP)NPN Single NMP

For complete documentation, see the data sheet

Product Description

2SA1709 is a Bipolar Transistor, -100V, -2A, Low VCE(sat), (PNP)NPN Single NMP for High-Voltage Switching Applications.

Features

- Adoption of FBET, MBIT processes
- High breakdown voltage, large current capacity
- Fast switching speed

Part Electrical Specifications

Product	Compliance	Status	Polarity	I _C Continuous (A)	V _{(BR)CEO} Min (V)	h _{FE} Min	h _{FE} Max	f _T Min (MHz)	P _{TM} Max (W)	Package Type
2SA1709S-AN	Pb-free	Active	PNP	2	100	140	280	-	1	NMP (Taping)
2SA1709T-AN	Pb-free	Active	PNP	2	100	200	400	-	1	NMP (Taping)

For more information please contact your local sales support at www.onsemi.com

Created on: 7/11/2015