



Product Overview

2N5684: 50 A, 80 V PNP Bipolar Power Transistor

For complete documentation, see the data sheet

Product Description

The Power 50A 80 V Bipolar NPN Transistor is designed for use in high power amplifier and switching circuit applications.

Features

- High Current Capability - I_C Continuous = 50 Amperes.
- DC Current Gain - $h_{FE} = 15-60$ @ $I_C = 25$ Adc
- Low Collector?Emitter Saturation Voltage - $V_{CE(sat)} = 1.0$ Vdc (Max) @ $I_C = 25$ Adc
- Pb-Free Packages are Available

Part Electrical Specifications

Product	Compliance	Status	Polarity	I_C Continuous (A)	$V_{(BR)CEO}$ Min (V)	h_{FE} Min	h_{FE} Max	f_T Min (MHz)	P_{TM} Max (W)	Package Type
2N5684G	Pb-free	Active	PNP	50	80	15	60	2	300	TO-204-2 / TO-3-2

For more information please contact your local sales support at www.onsemi.com

Created on: 7/11/2015