



Product Overview

BD136: 1.5 A, 45 V PNP Bipolar Power Transistor

For complete documentation, see the data sheet

Product Description

This series of plastic, medium-power PNP transistors are designed for use as audio amplifiers and drivers utilizing complementary or quasi complementary circuits.

Features

- DC Current Gain - $h_{FE} = 40$ (Min) @ $I_C = 0.15$ Adc
- BD 136, 138, 140 are complementary with BD 135, 137, 139
- Pb-Free Package is Available*

Part Electrical Specifications

Product	Compliance	Status	Polarity	I_C Continuous (A)	$V_{(BR)CEO}$ Min (V)	h_{FE} Min	h_{FE} Max	f_T Min (MHz)	P_{TM} Max (W)	Package Type
BD136G	Pb-free Halide free	NEW	PNP	1.5	45	40	250	-	12.5	TO-225-3

For more information please contact your local sales support at www.onsemi.com

Created on: 7/11/2015