



Product Overview

MBR60L45: Schottky Barrier Rectifier, L-Series, 60 A, 45 V

For complete documentation, see the data sheet

Product Description

This product is an enhanced Schottky Power Rectifier with lower V_f and higher surge to provide lower power loss and higher efficiency.

Features

- Low Forward Voltage
- Low Power Loss/High Efficiency
- High Surge Capacity
- 175°C Operating Junction Temperature
- 60 A Total (30 A Per Diode Leg)
- Guard-Ring for Stress Protection
- Mechanical Characteristics:
- Case: Epoxy, Molded
- Epoxy Meets UL 94 V0 @ 0.125 in
- Weight (Approximately): 1.9 Grams (TO220) and 4.3 Grams (TO247)

Benefits

- Better and higher efficiencies

Applications

- Power Supply Output Rectification
- Power Management
- Instrumentation

Part Electrical Specifications

Product	Compliance	Status	Configuration	V_{RRM} Min (V)	V_F Max (V)	I_{RM} Max (uA)	$I_{O(rec)}$ Max (A)	I_{FSM} Max (A)	t_{rr} Max (ns)	C_j Max (pF)	Package Type
MBR60L45CTG	Pb-free	Active	Common Cathode	45	0.73	1200	60	200			TO-220-3
MBR60L45WTG	Pb-free	Active	Common Cathode	45	0.73	1200	60	200			TO-247-3

For more information please contact your local sales support at www.onsemi.com

Created on: 7/11/2015