



Product Overview

LC898212XC: Auto Focus (AF) Controller

For complete documentation, see the data sheet

Product Description

This LSI is an Auto Focus (AF) control LSI. It consists of 1 system of feed back circuit for AF control.

Features

- Built-in equalizer circuit using digital operation :
AF control equalize circuit
Any coefficient can be specified by I²C I/F
- I²C Interface
- Built-in A/D converter :
Maximum 10-bit
Input 2 channel
- Built-in D/A converter :
8-bit Output
2-channel (Hall offset, Constant current Bias)
- Built-in OP Amp :
1 channel
Hall Amp
- Built-in OSC : 48MHz (Frequency adjustment function)
- Built-in PWM pulse generator circuit :
PWM circuit for AF control
- 1-chip motor driver : Saturation drive H bridge 1 channel
- Supply voltage :
Logic unit = Internal core typ 1.2V, AVDD (2.6V to 3.6V)
- Supply voltage :
Driver unit = VM (2.6V to 3.6V)

Part Electrical Specifications

Product	Compliance	Status	Type	V _M Min (V)	V _M Max (V)	V _{CC} Min (V)	V _{CC} Max (V)	I _O Max (A)	I _O Peak Max (A)	Step Reso- lution	Control Type	Feed- back Method	Current Sense	Regu- lator Output	Fault Detection	Flyback Protection	R _{DS(on)} Typ (Ω)	Package Type
LC898212XC-MH	Pb-free Halide free	Active	OIS/ AF	2.6	3.6	2.6	3.6	0.13	0.195		I2C			Yes			7.7	WLCSP-12 / WLP-12

For more information please contact your local sales support at www.onsemi.com

Created on: 7/11/2015