



Product Overview

MBRB30H60CT-1: Schottky Barrier Rectifier, H-Series, 60 V, 30 A

For complete documentation, see the data sheet

Product Description

Enhanced Schottky rectifiers with lower V_F , higher surge, and lower IR parameters

Features

- Low Forward Voltage
- High Surge Capacity
- 175°C Operating Junction Temperature
- 30A Total (15A Per Diode Leg)
- AEC-Q101 Qualified and PPAP Capable
- These are Pb-Free Packages
- NRVBB Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements

Benefits

- Low Power Loss/High Efficiency

Applications

- Output Rectification
- Power Management
- Instrumentation

End Products

- Power Supply

Part Electrical Specifications

Product	Compliance	Status	Configuration	V_{RRM} Min (V)	V_F Max (V)	I_{RM} Max (uA)	$I_{O(rec)}$ Max (A)	I_{FSM} Max (A)	t_{rr} Max (ns)	C_j Max (pF)	Package Type
MBRB30H60CT-1G	Pb-free	Active	Common Cathode	60	0.78	300	30	260	-	-	² I PAK-3
MBRB30H60CTT4G	Pb-free	Active	Common Cathode	60	0.78	300	30	260	-	-	² D PAK-3
	Halide free										
NRVBB30H60CTT4G	AEC Qualified	Active	Common Cathode	60	0.78	300	30	260	-	-	² D PAK-3
	PPAP Capable										
	Pb-free										
	Halide free										

For more information please contact your local sales support at www.onsemi.com

Created on: 7/11/2015