



## Product Overview

### MJE2955T: Bipolar Power Transistor, PNP, 10 A, 60 V, 75 Watt

For complete documentation, see the data sheet

#### Product Description

The Bipolar Power Transistor is designed for use in general-purpose amplifier and switching applications. The MJE2955T (PNP) and MJE3055T (NPN) are complementary devices.

#### Features

- DC Current Gain Specified to 10 Amperes
- High Current Gain - Bandwidth Product -  
 $f_T = 2.0 \text{ MHz (Min) @ } I_C$   
 $f_T = 500 \text{ mAdc}$
- Pb-Free Packages are Available

#### Part Electrical Specifications

Product	Compliance	Status	Polarity	$I_C$ Continuous (A)	$V_{(BR)CEO}$ Min (V)	$h_{FE}$ Min	$h_{FE}$ Max	$f_T$ Min (MHz)	$P_{TM}$ Max (W)	Package Type
MJE2955TG	Pb-free	Active	PNP	10	60	20	100	2	125	TO-220-3

For more information please contact your local sales support at [www.onsemi.com](http://www.onsemi.com)

Created on: 7/11/2015