



Product Overview

MBRF20200CT: Schottky Power Rectifier, Switch-mode, 20 A, 200 V

For complete documentation, see the data sheet

Product Description

The Schottky Rectifier employs the Schottky Barrier principle in a large metal to silicon power diode. State of the art geometry features epitaxial construction with oxide passivation and metal overlay contact. It is ideally suited for use in low voltage, high frequency switching power supplies, free wheeling diodes and polarity protection diodes.

Features

- Highly Stable Oxide Passivated Junction
- Very Low Forward Voltage Drop
- Matched Dual Die Construction
- High Junction Temperature Capability
- High dv/dt Capability
- Guardring for Stress Protection
- Epoxy Meets UL94, V_O at 1/8"
- Electrically Isolated. No Isolation Hardware Required.
- UL Recognized File #E69369

Mechanical Characteristics:

- Case: Epoxy, Molded

Part Electrical Specifications

Product	Compliance	Status	Configuration	V _{RRM} Min (V)	V _F Max (V)	I _{RM} Max (uA)	I _{O(rec)} Max (A)	I _{FSM} Max (A)	t _{rr} Max (ns)	C _j Max (pF)	Package Type
MBRF20200CTG	Pb-free	Active	Common Cathode	200	1	1000	20	150			TO-220 FULLPAK-3

For more information please contact your local sales support at www.onsemi.com

Created on: 7/11/2015