

Product Overview

MBRS4201: Schottky Power Rectifier, Surface Mount, Fast Soft-Recovery, 4.0 A, 200 V

For complete documentation, see the data sheet.

This Schottky Rectifier is a state-of-the-art high voltage fast-soft recovery Schottky device perfectly designed for use where ultra fast devices fall short in switching performance.

Features

- Lower Forward Voltage than any Ultrafast Rectifier: $V_F < 0.61$ V at 150C
- Fast Switching Speed: Reverse Recovery Time (t_{RR}) < 35 ns
- Soft Recovery Characteristics: Softness Factor (t_b/t_a) < 1
- Highly Stable Over Temperature
- Pb-Free Package is Available
- AEC-Q101 Qualified and PPAP Capable
- NRVB Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements

Applications

- Engine and Convenience Control Systems
- Motor Controls
- Battery Chargers and Switching Power Supplies

Part Electrical Specifications

Product	Compliance	Status	Configuration	V_{RRM} Min (V)	V_F Max (V)	I_{RM} Max (μ A)	$I_{O(rec)}$ Max (A)	I_{FSM} Max (A)	t_r Max (ns)	C_j Max (pF)	Package Type
MBRS4201T3G	AEC Qualified	Active	Single	200	0.8	0.35	4	100	35	-	SMC-2
	Pb-free										
	Halide free										
NRVBS4201T3G	AEC Qualified	Active	Single	200	0.8	0.35	4	100	35	-	SMC-2
	PPAP Capable										
	Pb-free										
	Halide free										

For more information please contact your local sales support at www.onsemi.com.

Created on: 10/23/2018