

Product Overview

NB3U23C: 1.2 V Dual Channel CMOS Buffer / Translator

For complete documentation, see the data sheet.

The NB3U23C is a 2-input, 2-output buffer/voltage translator for a UFS (Universal Flash Storage) application in a mobile phone. This dual channel CMOS buffer accepts 1.8 V CMOS input and translates it to 1.2 V CMOS output. The device is powered using single supply of 1.2 V $\pm 5\%$.

The NB3U23C is packaged in an ultra-small 6-pin SC70-6 package and a 6 pin thin UDFN package

Features

- Operating Frequency: 52 MHz (Max)
- Propagation Delay: 5 ns (Max)
- Low Standby Current: $< 10 \mu\text{A}$ at 1.2 V VDD
- Low Phase Noise Floor: -150 dBc/Hz (Typ)
- Low Phase Noise Floor: -150 dBc/Hz (Typ)
- Rise/Fall Times (tr/ta): 2 ns (Max)
- Operating Supply Voltage Range (VDD): 1.2 V $\pm 5\%$
- Operating Temperature Range (Industrial): -40°C to 85°C

Applications

- Computing and Peripherals
- Universal Flash Storage
- Portable and Wireless

End Products

- Smart Phones
- Tablets
- Camera
- E-readers

Part Electrical Specifications

Product	Compliance	Status	Type	Channels	Input / Output Ratio	Input Level	Output Level	V _{CC} Typ (V)	t _{jitter} RMS Typ (ps)	t _{skew} (o-o) Max (ps)	t _{pd} Typ (ns)	t _r & t _f Max (ps)	f _{max} Clock Typ (MHz)	f _{max} Data Typ (Mbps)	Package Type
NB3U23CMNTAG	Pb-free	Active	Buffer	2	1:1	CMOS	CMOS	1.2	0.15		5	2000			UDFN-6
	Halide free														
NB3U23CSQTCG	Pb-free	Active	Buffer	2	1:1	CMOS	CMOS	1.2	0.15		5	2000			SC-88-6 / SC-70-6 / SOT-363-6
	Halide free														

For more information please contact your local sales support at www.onsemi.com.

Created on: 7/22/2018