

## Product Overview

### MC74LCX14: Low Voltage CMOS Hex Inverter with 5.0 V-Tolerant Input and Schmitt Trigger Input

For complete documentation, see the data sheet.

The MC74LCX14 is a high performance hex inverter with Schmitt-Trigger inputs operating from a 2.7 to 3.6 V supply. High impedance TTL compatible inputs significantly reduce current loading to input drivers, while TTL compatible outputs offer improved switching noise performance. A  $V_I$  specification of 5.5 V allows MC74LCX14 inputs to be safely driven from 5 V devices.

Pin configuration and function are the same as the MC74LCX04, but the inputs have hysteresis and, with its Schmitt trigger function, the LCX14 can be used as a line receiver which will receive slow input signals.

### Features

- Designed for 2.3 V to 3.6 V  $V_{CC}$  Operation
- 5 V Tolerant Inputs - Interface Capability With 5 V TTL Logic
- LVTTTL Compatible
- LVCMOS Compatible
- 24 mA Balanced Output Sink and Source Capability
- Near Zero Static Supply Current (10  $\mu$ A) Substantially Reduces System Power Requirements
- Latch Performance Exceeds 500 mA
- Current Drive Capability is 24 mA at the Outputs
- Pin and Function Compatible with Other Standard Logic Families
- ESD Performance: HBM > 2000 V; Machine Model > 100 V

For more features, see the data sheet

### Part Electrical Specifications

Product	Compliance	Status	Type	Channels	$V_{CC}$ Min (V)	$V_{CC}$ Max (V)	$t_{pd}$ Max (ns)	$I_O$ Max (mA)	Package Type
MC74LCX14DG	Pb-free	Active	Inverter	6	2	3.6	6.5	24	SOIC-14
	Halide free								
MC74LCX14DR2G	Pb-free	Active	Inverter	6	2	3.6	6.5	24	SOIC-14
	Halide free								
MC74LCX14DTG	Pb-free	Active	Inverter	6	2	3.6	6.5	24	TSSOP-14
	Halide free								
MC74LCX14DTR2G	Pb-free	Active	Inverter	6	2	3.6	6.5	24	TSSOP-14
	Halide free								

For more information please contact your local sales support at [www.onsemi.com](http://www.onsemi.com).

Created on: 6/24/2018