



Product Overview

MC79L15: Linear Voltage Regulator, Negative, 15 V, 100 mA

For complete documentation, see the data sheet

Product Description

The MC79L00 negative linear voltage regulator is an inexpensive, easy-to-use device suitable for numerous applications requiring up to 100 mA. Like the higher powered MC7900 Series negative regulators, this linear voltage regulator features thermal shutdown and current limiting, making it remarkably rugged. In most applications, no external components are required for operation.

The MC79L00 linear voltage regulator is useful for on-card regulation or any other application where a regulated negative voltage at a modest current level is needed. This regulator offers substantial advantages over the common resistor/zener diode approach.

Features

- No External Components Required
- Internal Short Circuit Current Limiting
- Internal Thermal Overload Protection
- Low Cost
- Complementary Positive Regulators Offered (MC78L00 Series)
- Pb-Free Packages are Available

Part Electrical Specifications

Product	Compliance	Status	Output	Polarity	V _O (V)	I _O Typ (A)	V _I Max (V)	V _{DO} Typ (V)	I _q Typ (mA)	PSRR (dB)	Noise (μV _{rms})	Package Type
MC79L15ABDG	Pb-free Halide free	Active	Single	Negative	-15	0.1	-35	1.7	6	49	40	SOIC-8
MC79L15ABDR2G	Pb-free Halide free	Active	Single	Negative	-15	0.1	-35	1.7	6	49	40	SOIC-8
MC79L15ABPG	Pb-free Halide free	Active	Single	Negative	-15	0.1	-35	1.7	6	49	40	TO-92
MC79L15ABPRPG	Pb-free Halide free	Active	Single	Negative	-15	0.1	-35	1.7	6	49	40	TO-92
MC79L15ACDG	Pb-free Halide free	Active	Single	Negative	-15	0.1	-35	1.7	6	49	40	SOIC-8
MC79L15ACDR2G	Pb-free Halide free	Active	Single	Negative	-15	0.1	-35	1.7	6	49	40	SOIC-8
MC79L15ACPG	Pb-free Halide free	Active	Single	Negative	-15	0.1	-35	1.7	6	49	40	TO-92
MC79L15ACPRAG	Pb-free Halide free	Active	Single	Negative	-15	0.1	-35	1.7	6	49	40	TO-92
MC79L15ACPREG	Pb-free Halide free	Active	Single	Negative	-15	0.1	-35	1.7	6	49	40	TO-92
MC79L15ACPRPG	Pb-free Halide free	Active	Single	Negative	-15	0.1	-35	1.7	6	49	40	TO-92

For more information please contact your local sales support at www.onsemi.com

Created on: 7/11/2015