



## Product Overview

### MURA260T3: Power Rectifier, Ultra-Fast Recovery, 2 A, 600 V

For complete documentation, see the data sheet

#### Product Description

The Ultrafast Power Rectifier is ideally suited for high voltage, high frequency rectification or as free wheeling and protection diodes in surface mount applications, where compact size and weight are critical to the system.

#### Features

- Small Compact Surface Mountable Package with J-Bend Leads
- Rectangular Package for Automated Handling
- High Temperature Glass Passivated Junction
- Low Forward Voltage Drop (1.2 Volts Max @ 2.0 A, T<sub>J</sub> = 150°C)

Mechanical Characteristics:

- Case: Epoxy, Molded
- Weight: 70 mg (approximately)
- Finish: All External Surfaces Corrosion Resistant and Terminal Leads are Readily Solderable
- Lead and Mounting Surface Temperature for Soldering Purposes: 260°C Max. for 10 Seconds
- Shipped in 12 mm Tape and Reel, 5000 units per reel
- Polarity: Polarity Band Indicates Cathode Lead

#### Part Electrical Specifications

Product	Compliance	Status	Type	$I_{Q(rec)}$ Max (A)	$t_{rr}$ Max (ns)	$V_{RRM}$ Max (V)	$V_{FM}$ Max (V)	$I_{FSM}$ Max (A)	$I_R$ Max (mA)	Package Type
MURA260T3G	AEC Qualified Pb-free Halide free	Active	Ultrafast	2	75	600	1.45	35	0.005	SMA-2
SURA8260T3G	AEC Qualified PPAP Capable Pb-free Halide free	Active	Ultrafast	2	75	600	1.45	35	0.005	SMA-2

For more information please contact your local sales support at [www.onsemi.com](http://www.onsemi.com)

Created on: 7/11/2015