



Product Overview

MURF1660CT: Power Rectifier, Ultra-Fast Recovery, Switch-mode, 16 A, 600 V

For complete documentation, see the data sheet

Product Description

The Ultrafast Rectifier is designed for use in switching power supplies, inverters and as free wheeling diodes.

Features

- Ultrafast 60 Nanosecond Recovery Times
- 150°C Operating Junction Temperature
- Epoxy Meets UL94, V₀ @ 1/8"
- High Temperature Glass Passivated Junction
- Low Leakage Specified @ 150°C Case Temperature
- Current Derating @ Both Case and Ambient Temperatures
- Electrically Isolated. No Isolation Hardware Required.
- UL Recognized File #E69369

Mechanical Characteristics:

- Case: Epoxy, Molded
- Weight: 1.9 grams (approximately)

Part Electrical Specifications

Product	Compliance	Status	Type	I _{O(rec)} Max (A)	t _{rr} Max (ns)	V _{RRM} Max (V)	V _{FM} Max (V)	I _{FSM} Max (A)	I _R Max (mA)	Package Type
MURF1660CTG	Pb-free	Active	Ultrafast	16	60	600	1.5	100	0.5	TO-220 FULLPAK-3

For more information please contact your local sales support at www.onsemi.com

Created on: 7/11/2015