



Product Overview

NL7SZ58: Flexible Choice Logic (9 Configurable Functions), Inverting

For complete documentation, see the data sheet

Product Description

The NL7SZ58 is an advanced high-speed CMOS multifunction gate. The device allows the user to choose logic functions AND, OR, NAND, NOR, XOR, INVERT and BUFFER. The device has Schmitt-trigger inputs, thereby enhancing noise immunity. The NL7SZ58 input and output structures provide protection when voltages up to 7.0 V are applied, regardless of the supply voltage.

Features

- High Speed: $t_{PD} = 3.4 \text{ ns (Typ)}$ @ $V_{CC} = 5.0 \text{ V}$
- Low Power Dissipation: $ICC = 1 \text{ A (Maximum)}$ at $TA = 25^\circ\text{C}$
- Power Down Protection Provided on inputs
- Balanced Propagation Delays
- Overvoltage Tolerant (OVT) Input and Output Pins
- Ultra-Small Package
- This is a Pb-Free Device

Applications

- General Purpose Logic

End Products

- Handheld: PDA, Digital Cameras, GPS

Part Electrical Specifications

Product	Compliance	Status	Type	Channels	V_{CC} Min (V)	V_{CC} Max (V)	t_{pd} Max (ns)	I_O Max (mA)	Package Type
NL7SZ58DFT2G	Pb-free Halide free	Active	SmartGate	3	1.65	5.5	2.5	32	SC-88-6 / SC-70-6 / SOT-363-6
NLV7SZ58DFT2G	AEC Qualified PPAP Capable Pb-free Halide free	Active	SmartGate	3	1.65	5.5	2.5	32	SC-88-6 / SC-70-6 / SOT-363-6

For more information please contact your local sales support at www.onsemi.com

Created on: 7/11/2015