



Product Overview

NTR5198NL: Power MOSFET 60V 2.2A 155 mOhm Single N-Channel SOT-23

For complete documentation, see the data sheet

Product Description

Power MOSFET 60V 2.2A 155 mOhm Single N-Channel SOT-23

FeaturesBenefits

- Low RDS(on)
- High Current Capability
- These Devices are PbFree, Halogen Free/BFR Free and are RoHS Compliant
- Minimize Conduction Losses

Part Electrical Specifications

Product	Compliance	Status	Channel Polarity	Configuration	V _{DS} (BR) Min (V)	V _{GS} Max (V)	V _{GS} (th) Max (V)	I _D Max (A)	P _D Max (W)	r _{DS(on)} Max @ V _{GS} = 2.5 V (m)	r _{DS(on)} Max @ V _{GS} = 4.5 V (m)	r _{DS(on)} Max @ V _{GS} = 10 V (m)	Q _g Typ @ V _{GS} = 4.5 V (nC)	Q _g Typ @ V _{GS} = 10 V (nC)	Q _{gd} Typ @ V _{GS} = 4.5 V (nC)	Q _{rr} Typ (nC)	C _{iss} Typ (pF)	C _{oss} Typ (pF)	C _{rss} Typ (pF)	Package Type
NTR5198NLT1G	Pb-free Halide free	Active	N-Channel	Single	60	20	2.5	2.2	1.5		205		3	5.4			191	22	17	SOT-23-3
NTR5198NLT3G	Pb-free Halide free	Active	N-Channel	Single	60	20	2.5	2.2	1.5		205		3	5.4			191	22	17	SOT-23-3

For more information please contact your local sales support at www.onsemi.com

Created on: 7/11/2015