



## Product Overview

### NVMFS4C05N: Power MOSFET 30V, 116A, 3.4 mOhm, Single N-Channel, SO8-FL, Logic Level.

For complete documentation, see the data sheet

#### Product Description

Automotive Power MOSFET in a 5x6mm flat lead package designed for compact and efficient designs and including high thermal performance. Wettable Flank Option available for Enhanced Optical Inspection. AEC-Q101 Qualified MOSFET and PPAP capable suitable for automotive applications.

Features	Benefits
<ul style="list-style-type: none"> <li>Low on-resistance</li> <li>Low Capacitance</li> <li>Low gate charge</li> <li>u8FL package with 3.3 x 3.3 mm footprint</li> <li>AEC-Q101 qualified</li> <li>Wettable flank (WF) option</li> </ul>	<ul style="list-style-type: none"> <li>minimizes conduction losses</li> <li>minimizes driver losses</li> <li>minimizes switching losses</li> <li>very small footprint enabling smaller PCBs and modules</li> <li>suitable for automotive applications</li> <li>facilitates Automated Optical Inspection of device-to-PCB solder joints</li> </ul>

Applications	End Products
<ul style="list-style-type: none"> <li>Reverse battery protection</li> <li>DC-DC converter output driver</li> </ul>	<ul style="list-style-type: none"> <li>HID and LED lighting</li> <li>Infotainment Power Supplies</li> </ul>

#### Part Electrical Specifications

Product	Compliance	Status	Channel Polarity	Configuration	$V_{DS}$ Min (V)	$V_{GS}$ Max (V)	$V_{GS(th)}$ Max (V)	$I_D$ Max (A)	$P_D$ Max (W)	$r_{DS(on)}$ Max @ $V_{GS}=2.5V$ (m)	$r_{DS(on)}$ Max @ $V_{GS}=4.5V$ (m)	$r_{DS(on)}$ Max @ $V_{GS}=10V$ (m)	$Q_g$ Typ @ $V_{GS}=4.5V$ (nC)	$Q_g$ Typ @ $V_{GS}=10V$ (nC)	$Q_{gd}$ Typ @ $V_{GS}=4.5V$ (nC)	$Q_{rr}$ Typ (nC)	$C_{iss}$ Typ (pF)	$C_{oss}$ Typ (pF)	$C_{rss}$ Typ (pF)	Package Type
NVMFS4C05NT1G	AEC Qualified PPAP Capable Pb-free Halide free	Active	N-Channel	Single	30	20	2.2	116	92		5	3.4	14	30	5.9	30.2	197.2	121.5	59	SO-8FL / DF N-5
NVMFS4C05NT3G	AEC Qualified PPAP Capable Pb-free Halide free	Active	N-Channel	Single	30	20	2.2	116	92		5	3.4	14	30	5.9	30.2	197.2	121.5	59	SO-8FL / DF N-5
NVMFS4C05NWFT1G	AEC Qualified PPAP Capable Pb-free Halide free	Active	N-Channel	Single	30	20	2.2	116	92		5	3.4	14	30	5.9	30.2	197.2	121.5	59	SO-8FL / DF N-5
NVMFS4C05NWFT3G	AEC Qualified PPAP Capable Pb-free Halide free	Active	N-Channel	Single	30	20	2.2	116	92		5	3.4	14	30	5.9	30.2	197.2	121.5	59	SO-8FL / DF N-5

For more information please contact your local sales support at [www.onsemi.com](http://www.onsemi.com)

Created on: 7/11/2015