



Product Overview

SCH1430: N-Channel Power MOSFET, 20V, 2A, 125mΩ, Single SCH6

For complete documentation, see the data sheet

Product Description

SCH1430 is an N-Channel Power MOSFET, 20V, 2A, 125mΩ, Single SCH6 for General-Purpose Switching Device Application.

Features

- 1.8V drive
- Halogen free compliance
- Protection diode in

Part Electrical Specifications

Product	Compliance	Status	Channel Polarity	Configuration	$V_{DS(BR)Min}$ (V)	$V_{GSMax}$ (V)	$V_{GS(th)Max}$ (V)	$I_{DMax}$ (A)	$P_{DMax}$ (W)	$r_{DS(on)Max @ V_{GS} = 2.5V(m)}$	$r_{DS(on)Max @ V_{GS} = 4.5V(m)}$	$r_{DS(on)Max @ V_{GS} = 10V(m)}$	$Q_g Typ @ V_{GS} = 4.5V(nC)$	$Q_g Typ @ V_{GS} = 10V(nC)$	$Q_{gd} Typ @ V_{GS} = 4.5V(nC)$	$Q_{rr} Typ (nC)$	$C_{iss} Typ (pF)$	$C_{oss} Typ (pF)$	$C_{rss} Typ (pF)$	Packaging Type
SCH1430-TL-H	Pb-free Halide free	Active	N-Channel	Single	20	12	1.3	2	0.8	190	125		1.8	0.55			128	28	21	SO-T-563 / SCH-6

For more information please contact your local sales support at [www.onsemi.com](http://www.onsemi.com)

Created on: 7/11/2015