



Product Overview

SFT1450: N-Channel Power MOSFET, 40V, 21A, 28mΩ, Single TP/TP-FA

For complete documentation, see the data sheet

Product Description

SFT1450 is an N-Channel Power MOSFET, 40V, 21A, 28mΩ, Single TP/TP-FA for General-Purpose Switching Device Applications.

Features

- ON-resistance $R_{DS(on)1} = 21m\Omega$ (typ)
- Input Capacitance $C_{iss} = 715pF$ (typ)
- 4.5V drive
- Halogen free compliance
- Protection diode in

Part Electrical Specifications

Product	Compliance	Status	Channel Polarity	Configuration	V_{DS} Min (V)	V_{GS} Max (V)	V_{GS} Min (V)	I_D Max (A)	P_D Max (W)	$r_{DS(on)}$ Max @ $V_{GS} = 2.5V$ (m)	$r_{DS(on)}$ Max @ $V_{GS} = 4.5V$ (m)	$r_{DS(on)}$ Max @ $V_{GS} = 10V$ (m)	Q_g Typ @ $V_{GS} = 4.5V$ (nC)	Q_g Typ @ $V_{GS} = 10V$ (nC)	Q_{gd} Typ @ $V_{GS} = 4.5V$ (nC)	Q_{rr} Typ (nC)	C_{iss} Typ (pF)	C_{oss} Typ (pF)	C_{rss} Typ (pF)	Packaging Type
SFT1450-H	Pb-free Halide free	Active	N-Channel	Single	40	20	2.6	21	1		56	28		14.4	3.1		715	85	65	IPAK / TP
SFT1450-TL-H	Pb-free Halide free	Active	N-Channel	Single	40	20	2.6	21	1		56	28		14.4	3.1		715	85	65	DPAK / TP-FA

For more information please contact your local sales support at www.onsemi.com

Created on: 7/11/2015