General Purpose Transistor

NPN Silicon

BC846BM3T5G, NSVBC846BM3T5G

Features

• Moisture Sensitivity Level: 1

• ESD Rating: Human Body Model: >4000 V

Machine Model: >400 V

 NSV Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements; AEC-Q101 Qualified and PPAP Capable

• This is a Pb-Free Device

MAXIMUM RATINGS

Rating	Symbol	Value	Unit
Collector-Emitter Voltage	V _{CEO}	65	Vdc
Collector-Base Voltage	V _{CBO}	80	Vdc
Emitter-Base Voltage	V _{EBO}	6.0	Vdc
Collector Current – Continuous	Ic	100	mAdc

THERMAL CHARACTERISTICS

Characteristic	Symbol	Max	Unit
Total Device Dissipation FR-5 Board (Note 1) T _A = 25°C	P _D	265	mW
Derate above 25°C		2.1	mW/°C
Thermal Resistance, Junction to Ambient (Note 1)	$R_{ hetaJA}$	470	°C/W
Total Device Dissipation Alumina Substrate (Note 2) T _A = 25°C	P _D	640	mW
Derate above 25°C		5.1	mW/°C
Thermal Resistance, Junction to Ambient (Note 2)	$R_{ heta JA}$	195	°C/W
Junction and Storage Temperature Range	T _J , T _{stg}	–55 to +150	°C

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

1


1. FR-5 = $1.0 \times 0.75 \times 0.062$ in.

2. Alumina = $0.4 \times 0.3 \times 0.024$ in. 99.5% alumina.



ON Semiconductor®

www.onsemi.com



MARKING DIAGRAM



SOT-723 CASE 631AA STYLE 1



1B = Specific Device Code M = Date Code

ORDERING INFORMATION

Device	Package	Shipping [†]
BC846BM3T5G	SOT-723 (Pb-Free)	8000 / Tape & Reel
NSVBC846BM3T5G	SOT-723 (Pb-Free)	8000 / Tape & Reel

†For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

BC846BM3T5G, NSVBC846BM3T5G

ELECTRICAL CHARACTERISTICS (T_A = 25°C unless otherwise noted)

Characteristic	Symbol	Min	Тур	Max	Unit
OFF CHARACTERISTICS	•		•	•	
Collector - Emitter Breakdown Voltage (I _C = 10 mA)	V _{(BR)CEO}	65	_	_	V
Collector – Emitter Breakdown Voltage ($I_C = 10 \mu A, V_{EB} = 0$)	V _{(BR)CES}	80	_	-	V
Collector – Base Breakdown Voltage ($I_C = 10 \mu A$)	V _{(BR)CBO}	80	_	-	V
Emitter – Base Breakdown Voltage (I _E = 1.0 μA)	V _{(BR)EBO}	6.0	_	-	V
Collector Cutoff Current $(V_{CB} = 30 \text{ V})$ $(V_{CB} = 30 \text{ V}, T_A = 150^{\circ}\text{C})$	I _{CBO}	-	- -	15 5.0	nA μA
Base Peak Current $(t \le 1 \text{ s})$	I _{BM}	-	_	200	mA
ON CHARACTERISTICS					
DC Current Gain $ (I_C = 10 \ \mu\text{A}, \ V_{CE} = 5.0 \ \text{V}) $ $ (I_C = 2.0 \ \text{mA}, \ V_{CE} = 5.0 \ \text{V}) $	h _{FE}	_ 200	150 290	- 450	_
Collector – Emitter Saturation Voltage (I_C = 10 mA, I_B = 0.5 mA) (I_C = 100 mA, I_B = 5.0 mA)	V _{CE(sat)}	-	- -	0.25 0.6	V
Base – Emitter Saturation Voltage (I_C = 10 mA, I_B = 0.5 mA) (I_C = 100 mA, I_B = 5.0 mA)	V _{BE(sat)}	- -	0.7 0.9	-	V
Base – Emitter Voltage (I_C = 1.0 mA, V_{CE} = 5.0 V) (I_C = 2.0 mA, V_{CE} = 5.0 V) (I_C = 10 mA, V_{CE} = 5.0 V)	V _{BE(on)}	550 580 –	645 660 –	700 700 770	mV
SMALL-SIGNAL CHARACTERISTICS					
Current – Gain – Bandwidth Product (I _C = 10 mA, V _{CE} = 5.0 Vdc, f = 100 MHz)	f _T	100	_	-	MHz
Output Capacitance (V _{CB} = 10 V, f = 1.0 MHz)	C _{obo}	_	_	4.5	pF
Noise Figure (I _C = 0.2 mA, V _{CE} = 5.0 Vdc, R _S = 2.0 k Ω , f = 1.0 kHz, BW = 200 Hz)	NF	-	_	10	dB

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

BC846BM3T5G, NSVBC846BM3T5G

TYPICAL CHARACTERISTICS




Figure 1. DC Current Gain

Figure 2. Collector-Emitter Saturation Voltage




Figure 3. Base-Emitter Saturation Voltage

Figure 4. Base-Emitter "On" Voltage




Figure 5. Base–Emitter Temperature Coefficient

Figure 6. Collector Saturation Region

BC846BM3T5G, NSVBC846BM3T5G

TYPICAL CHARACTERISTICS




Figure 7. Capacitances

Figure 8. Current-Gain-Bandwidth Product







SOT-723 1.20x0.80x0.50, 0.40P CASE 631AA ISSUE E


DATE 24 JAN 2024

NOTES:


- 1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 2018.
- 2. CONTROLLING DIMENSION: MILLIMETERS.
- 3, MAXIMUM LEAD THICKNESS INCLUDES LEAD FINISH, MINIMUM LEAD THICKNESS IS THE MINIMUM THICKNESS OF BASE MATERIAL.
- 4. DIMENSIONS D AND E DO NOT INCLUDE MOLD FLASH, PROTRUSIONS OR GATE BURRS.







MILLIMETERS DIM MIN. $N\square M$. MAX. 0.45 0.50 0.55 Α 0.15 0.21 0.27 b 0.25 0.31 0.37 b1 0.07 0.12 0.17 \subset D 1.25 1.15 1.20 Ε 0.75 0.80 0.85 0.40 BSC е Н 1.20 1.15 1.25 0.29 REF L L2 0.15 0.20 0.25



RECOMMENDED MOUNTING FOOTPRINT

*For additional information on our Pb-Free strategy and soldering details, please download the DN Semiconductor Soldering and Mounting Techniques Reference Manual, SDLDERRM/D.

GENERIC MARKING DIAGRAM*



XX = Specific Device Code
M = Date Code

*This information is generic. Please refer to device data sheet for actual part marking. Pb-Free indicator, "G" or microdot "•", may or may not be present. Some products may not follow the Generic Marking.

STYLE 1: STYLE 2: STYLE 3: STYLE 4: STYLE 5: PIN 1. GATE 2. SOURCE PIN 1. BASE PIN 1. ANODE PIN 1. ANODE PIN 1. CATHODE 2 FMITTER N/C
 CATHODE 2 CATHODE 2. ANODE 3. COLLECTOR 3. CATHODE 3. ANODE 3. DRAIN

DESCRIPTION:	SOT-723 1.20x0.80x0.50, 0.40P		PAGE 1 OF 1
DOCUMENT NUMBER:	98AON12989D	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.	

onsemi and ONSemi are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. onsemi does not convey any license under its patent rights nor the rights of others.

onsemi, Onsemi, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. Onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA class 3 medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:

 $\textbf{Technical Library:} \ \underline{www.onsemi.com/design/resources/technical-documentation}$

onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support

For additional information, please contact your local Sales Representative at

www.onsemi.com/support/sales