

ESD Protection Diode

Micro-Packaged Diodes for ESD Protection ESD7382MUT5G

The ESD7382 is designed to protect voltage sensitive components that require ultra-low capacitance from ESD and transient voltage events. Excellent clamping capability, low capacitance, low leakage, and fast response time, make these parts ideal for ESD protection on designs where board space is at a premium. Because of its low capacitance, it is suited for use in high frequency designs such as USB 2.0 high speed and antenna line applications.



• Ultra-Low Capacitance: 0.37 pF

• Low Clamping Voltage

• Small Body Outline Dimensions: 0.60 mm x 0.30 mm

Low Body Height: 0.3 mmStand-off Voltage: 5.0 V

• Low Leakage

• Insertion Loss: 0.030 dBm

• Response Time is < 1 ns

Low Dynamic Resistance < 1 Ω
 IEC61000-4-2 Level 4 ESD Protection

• These Devices are Pb-Free, Halogen Free/BFR Free and are RoHS Compliant

Typical Applications

• GPIO and Power Line Protection

MAXIMUM RATINGS

Rating	Symbol	Value	Unit
IEC 61000-4-2 (ESD) Contact Air		±20 ±20	kV
Total Power Dissipation on FR-5 Board (Note 1) @ T _A = 25°C Thermal Resistance, Junction-to-Ambient	P_{D} $R_{ hetaJA}$	250 400	mW °C/W
Junction and Storage Temperature Range	T _J , T _{stg}	-40 to +125	°C
Lead Solder Temperature – Maximum (10 Second Duration)	TL	260	°C

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

1. $FR-5 = 1.0 \times 0.75 \times 0.62$ in.

1 O 2 Cathode Anode

MARKING DIAGRAM

PIN 1



X3DFN2 CASE 152AF



2 = Specific Device Code (Rotated 270°)

M = Date Code

ORDERING INFORMATION

Device	Package	Shipping [†]
ESD7382MUT5G	X3DFN2 (Pb-Free)	10,000 / Tape & Reel

†For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.


1

ELECTRICAL CHARACTERISTICS

(T_A = 25°C unless otherwise noted)

(//	,		
Symbol	Parameter		
I _{PP}	Maximum Reverse Peak Pulse Current		
V _C	Clamping Voltage @ I _{PP}		
V_{RWM}	Working Peak Reverse Voltage		
I _R	Maximum Reverse Leakage Current @ V _{RWM}		
V_{BR}	Breakdown Voltage @ I _T		
I _T	Test Current		

^{*}See Application Note AND8308/D for detailed explanations of datasheet parameters.



ELECTRICAL CHARACTERISTICS (T_A = 25°C unless otherwise specified)

Parameter	Symbol	Conditions	Min	Тур	Max	Unit
Reverse Working Voltage	V_{RWM}				5.0	V
Breakdown Voltage (Note 2)	V_{BR}	I _T = 1 mA	5.2			V
Reverse Leakage Current	I _R	V _{RWM} = 5.0 V			1.0	μΑ
Clamping Voltage (Note 3)	V _C	I _{PP} = 1 A			8.0	V
Clamping Voltage (Note 3)	V _C	I _{PP} = 3 A			10	V
ESD Clamping Voltage	V _C	Per IEC61000-4-2	See Figures 1 and 2			
Junction Capacitance	СЈ	$V_R = 0 \text{ V, f} = 1 \text{ Mhz}$ $V_R = 0 \text{ V, f} < 1 \text{ GHz}$		0.37 0.25	0.55 0.55	pF
Dynamic Resistance	R_{DYN}	TLP Pulse		0.32		Ω
Insertion Loss		f = 1 Mhz f = 8.5 GHz		0.030 0.573		dB

- 2. Breakdown voltage is tested from pin 1 to 2 and pin 2 to 1.
- 3. Non-repetitive current pulse at $T_A = 25$ °C, per IEC61000-4-5 waveform.





Figure 1. ESD Clamping Voltage Screenshot Positive 8 kV Contact per IEC61000-4-2

Figure 2. ESD Clamping Voltage Screenshot Negative 8 kV Contact per IEC61000-4-2



FREQUENCY (Hz)
Figure 5. RF Insertion Loss

1.E+08

1.E+09


1.E+07

-8

-9 -10 1.E+06

FREQUENCY
Figure 6. Capacitance over Frequency

2.E+09 2.E+09 3.E+09 3.E+09



1.E+10

0.1

0.0 0.E+00

5.E+08

1.E+09

Figure 7. Positive TLP I-V Curve

Figure 8. Negative TLP I-V Curve

IEC 61000-4-2 Spec.

Level	Test Volt- age (kV)	First Peak Current (A)	Current at 30 ns (A)	Current at 60 ns (A)
1	2	7.5	4	2
2	4	15	8	4
3	6	22.5	12	6
4	8	30	16	8




Figure 9. IEC61000-4-2 Spec




Figure 10. Diagram of ESD Test Setup

ESD Voltage Clamping

For sensitive circuit elements it is important to limit the voltage that an IC will be exposed to during an ESD event to as low a voltage as possible. The ESD clamping voltage is the voltage drop across the ESD protection diode during an ESD event per the IEC61000-4-2 waveform. Since the IEC61000-4-2 was written as a pass/fail spec for larger systems such as cell phones or laptop computers it is not

clearly defined in the spec how to specify a clamping voltage at the device level. **onsemi** has developed a way to examine the entire voltage waveform across the ESD protection diode over the time domain of an ESD pulse in the form of an oscilloscope screenshot, which can be found on the datasheets for all ESD protection diodes. For more information on how **onsemi** creates these screenshots and how to interpret them please refer to AND8307/D.






Figure 11. 8 X 20 µs Pulse Waveform


PACKAGE DIMENSIONS

X3DFN2 0.62x0.32x0.24, 0.35P

CASE 152AF ISSUE C








NOTES:

- I. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 1994.
- 2. CONTROLLING DIMENSION: MILLIMETERS
- 3. 0201

	MILLIMETERS		
DIM	MIN.	N□M.	MAX.
А	0.25	0.29	0.33
A1	0.00		0.05
A2	0.14	0.24	0.34
b	0.22	0.25	0.28
b2	0.150 REF		
D	0.58	0.62	0.66
E	0.28	0.32	0.36
е	0.355 BSC		
L2	0.17	0.20	0.23
L3	0.050 REF		



For additional information on our Pb-Free strategy and soldering details, please download the □N Semiconductor Soldering and Mounting Techniques Reference Manual, S□LDERRM/D.

onsemi, ONSEMI, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. Onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any EDA class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Sho

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:

Technical Library: www.onsemi.com/design/resources/technical-documentation onsemi Website: www.onsemi.com/design/resources/technical-documentation on the first of the state of the state

ONLINE SUPPORT: www.onsemi.com/support

For additional information, please contact your local Sales Representative at www.onsemi.com/support/sales