4-Channel Low Capacitance Dual-Voltage ESD Protection Array

Features

- 3 Channels of Low Voltage ESD Protection
- 1 Channel of High Voltage ESD Protection
- Provides ESD Protection to IEC61000-4-2 Level 4: ±8 kV Contact Discharge (Pins 1-3) ±15 kV Contact Discharge (Pin 4)
- Low Channel Input Capacitance
- Minimal Capacitance Change with Temperature and Voltage
- High Voltage Zener Diode Protects Supply Rail
- No Need for External Bypass Capacitors
- Each I/O Pin Can Withstand Over 1000 ESD Strikes*
- These Devices are Pb–Free, Halogen Free/BFR Free and are RoHS Compliant



NOTE: Note: Pins 5, and 6 to 8 are connected to a common substrate.

Figure 1. Electrical Schematic

*Standard test condition is IEC61000-4-2 level 4 test circuit with each pin subjected to ±8 kV contact discharge for 1000 pulses. Discharges are timed at 1 second intervals and all 1000 strikes are completed in one continuous test run. The part is then subjected to standard production test to verify that all of the tested parameters are within spec after the 1000 strikes.



ON Semiconductor®

http://onsemi.com





ORDERING INFORMATION

See detailed ordering and shipping information in the package dimensions section on page 2 of this data sheet.



Figure 2. Typical Application

PIN DESCRIPTIONS

4-CHANNEL, 8-LEAD, uDFN-8 PACKAGE				
Pin	Name	Туре	Description	
1	CH1	I/O	LV Low-capacitance ESD Channel	
2	CH2	I/O	LV Low-capacitance ESD Channel	
3	СНЗ	I/O	LV Low-capacitance ESD Channel	
4	V _{CC}	$HV V_{DD}$	HV ESD Channel	
5	GND		Ground	
6	V _N		Negative Voltage Supply Rail	
7	V _N		Negative Voltage Supply Rail	
8	V _N		Negative Voltage Supply Rail	
DAP	GND		Die Attach Pad (Ground)	

ORDERING INFORMATION

Device (Note 1)	# of Channels	Leads	Part Marking	Package	Shipping [†]
ESD7554MUT2G	4	8	30V	uDFN-8, 0.4 mm (Pb-Free)	Tape & Reel

+For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

1. Parts are shipped in Tape and Reel form unless otherwise specified.

SPECIFICATIONS

ABSOLUTE MAXIMUM RATINGS

Parameter	Rating	Unit
DC Voltage on Low-voltage Pins	6	V
DC Voltage on High-voltage Pins (V _{CC} pin)	29	V
Operating Temperature Range	-40 to +85	°C
Storage Temperature Range	-65 to +150	°C

Stresses exceeding Maximum Ratings may damage the device. Maximum Ratings are stress ratings only. Functional operation above the Recommended Operating Conditions is not implied. Extended exposure to stresses above the Recommended Operating Conditions may affect device reliability.

STANDARD OPERATING CONDITIONS

Parameter	Rating	Unit
Operating Temperature Range	-40 to +85	°C

ELECTRICAL OPERATING CHARACTERISTICS (See Note 2)

Symbol	Parameter	Conditions	Min	Тур	Max	Unit
V _F	LV Diode Reverse Voltage (Positive Voltage)	I _F = 10 mA; T _A = 25°C	6.8	8.2	9.2	V
	LV Diode Forward Voltage (Negative Voltage)	I _F = 10 mA; T _A = 25°C	-1.05	-0.9	-0.6	V
I _{LEAK}	LV Channel Leakage Current (Pins 1 and 2)	$ \begin{array}{l} T_A = -30^\circ C \text{ to } 65^\circ C; \ V_{IN} = 3.3 \text{V}, \\ V_N = 0 \text{V} \end{array} $			100	nA
	LV Channel Leakage Current (Pin 3 only)	T_{A} = -30°C to 65°C; V_{IN} = 3.3 V, V_{N} = 0 V			100	nA
C _{IN}	LV Channel Input Capacitance	At 1 MHz, V_N = 0 V, V_{IN} = 1.65 V		1.2	1.5	pF
ΔC _{IN}	LV Channel Input Capacitance Matching	At 1 MHz, V _N = 0 V, V _{IN} = 1.65 V		0.02		pF
I _{LEAK_HV}	HV Channel Leakage Current	$T_A = 25^{\circ}C; V_{CC} = 28 \text{ V}, V_N = 0 \text{ V}$		0.1	1.0	mA
C _{IN_HV}	HV Channel Input Capacitance	At 1 MHz, $V_N = 0V$, $V_{IN} = 2.5 V$		30		pF
V _{F_HV}	HV Diode Breakdown Voltage Positive Voltage	I _F = 10 mA; T _A = 25°C	30		35	V
V _{ESD}	ESD Protection Peak Discharge Voltage at any channel input, in system Contact discharge per IEC 61000-4-2 standard	T _A = 25°C	±8 (Pin 1–3) ±15 (Pin 4)			kV
V _{CL}	LV Channel Clamp Voltage (Pin 1–3) Positive Transients Negative Transients	T_A = 25°C, I _{PP} = 1 A, t _P = 8/20 µS		+9.64 –1.75		V V
R _{DYN}	Dynamic Resistance LV Channel Positive Transients LV Channel Negative Transients HV Channel Positive Transients HV Channel Negative Transients	I _{PP} = 1 A, t _P = 8/20 μS Any I/O pin to Ground		0.72 0.59 4.00 0.20		Ω

2. All parameters specified at $T_A = -40^{\circ}C$ to +85°C unless otherwise noted.

PERFORMANCE INFORMATION

Input channel capacitance performance curves for low voltage pins



Figure 4. Typical Variation of C_{IN} vs. Temp (Low Voltage Inputs, f = 1 MHz, V_N = 0 V)

PERFORMANCE INFORMATION

Typical filter performance for low voltage pins Nominal conditions unless specified; otherwise, 50 Ω environment



Figure 6. Channel 2 vs. All GND Pins (0 V DC Bias)

PERFORMANCE INFORMATION

Typical filter performance for low voltage pins Nominal conditions unless specified; otherwise, 50 Ω environment





ONSEM¹.

€	UDFN8, 1.7x1.35, 0.4P			
	ISSUE A			
SCALE 4:1			DATE 11 AU	G 2022
SCALE 4:1 2X PIN AI REFERENCE 2X O 10 C TOP VIEW TOP VIEW TOP VIEW	NOTES: 1. DIMENSIONING ASME Y14.5M, 2. CONTROLLING 3. DIMENSION & TERMINAL AN: 0.15 AND 0.25 TIP. 4. COPLANARITY PADS AS WEL EXPOSED CU MOLD CMPD	AND TI 2004. DIMENS APPLIE D IS ME MM FOR APPLIE L AS T DIM A	DLERANCING PER IDN: MILLIMETER S TO PLATED ASURED BETWER M THE TERMINAL HE TERMINALS. MILLIMETERS MIN. MAX. 0.45 0.55	RS. EN JSED
NUTE 4 SIDE VIEW	PLANE DETAIL B ALTERNATE CONSTRUCTIONS	AI A3 b	0.00 0.05 0.13 REF 0.15 0.25	
DETAIL A $D2 - 1$ $8 \times L$ $D2 - 1$ $8 \times L$ $C - 1$ $8 \times L$ $C - 1$ $8 \times K$ B $8 \times K$ B $B \times K$ B	DETAIL A ALTERNATE CONSTRUCTIONS	D D2 E E2 e K L L1	1.70 BSC 1.10 1.30 1.35 BSC 0.30 0.50 0.40 BSC 0.15 0.20 0.30 0.05	
GENERIC	PACKAGE		40 - 8X 0.40	
MARKING DIAGRAMS*	8X 0.6 M[* For additional and soldering Semiconductor Reference Mai	RECOMI JUNTING I informatio details, pl Soldering hual, SDLDE	MENDED FOOTPRINT* n on our Pb-Free str ease download the DN and Mounting Techniqu RRM/D.	~ategy .es

DOCUMENT NUMBER:	98AON47060E	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.		
DESCRIPTION:	UDFN8, 1.7x1.35, 0.4P		PAGE 1 OF 1	

onsemi and ONSEMI: are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. onsemi does not convey any license under its patent rights nor the rights of others.

onsemi, ONSEMI, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi's product/patent coverage may be accessed at <u>www.onsemi.com/site/pdf/Patent-Marking.pdf</u>. onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or indental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification. Buyer shall indemnify and hold onsemi and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs,

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:

Technical Library: www.onsemi.com/design/resources/technical-documentation onsemi Website: www.onsemi.com

ONLINE SUPPORT: <u>www.onsemi.com/support</u> For additional information, please contact your local Sales Representative at <u>www.onsemi.com/support/sales</u>