ON Semiconductor

Is Now

Onsemi

To learn more about onsemi[™], please visit our website at <u>www.onsemi.com</u>

onsemi and ONSEMI. and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product factures, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and asfety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or by customer's technical experts. onsemi products and actal performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use onsemi products for any such unintended or unauthorized application, Buyer shall indemnify and hold onsemi and its officers, employees, subsidiari

EEPROM Serial 1-Kb Microwire

Description

The CAT93C46R is a 1–Kb Microwire Serial EEPROM device which is organized as either 64 registers of 16 bits or 128 registers of 8 bits, as determined by the state of the ORG pin. The CAT93C46R features sequential read and self-timed internal write with auto-clear. On-chip Power–On Reset circuitry protects the internal logic against powering up in the wrong state.

In contrast to the CAT93C46, the CAT93C46R features an internal instruction clock counter which provides improved noise immunity for Write/Erase commands.

Features

- High Speed Operation: 4 MHz @ 5 V, 2 MHz @ 1.8 V
- 1.8 V to 5.5 V Supply Voltage Range
- Selectable x8 or x16 Memory Organization
- Sequential Read
- Software Write Protection
- Power-up Inadvertant Write Protection
- Low Power CMOS Technology
- 1,000,000 Program/Erase Cycles
- 100 Year Data Retention
- Industrial Temperature Range
- 8-pin PDIP, SOIC, TSSOP and 8-pad TDFN Packages
- This Device is Pb-Free, Halogen Free/BFR Free and RoHS Compliant*




Figure 1. Functional Symbol

*For additional information on our Pb–Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.



ON Semiconductor®

www.onsemi.com





PDIP-8 L SUFFIX CASE 646AA





SOIC-8 V SUFFIX CASE 751BD TDFN-8** VP2 SUFFIX CASE 511AK

PIN CONFIGURATION

CS ⊞ 01 SK ⊞	
DO III	GND

PDIP (L), SOIC (V), TSSOP (Y), TDFN (VP2)**

(Top View)

** Not recommended for new designs

PIN FUNCTION

Pin Name	Function			
CS	Chip Select			
SK	Clock Input			
DI	Serial Data Input			
DO	Serial Data Output			
V _{CC}	Power Supply			
GND	Ground			
ORG	Memory Organization			
NC	No Connection			

Note: When the ORG pin is connected to V_{CC} , the x16 organization is selected. When it is connected to ground, the x8 pin is selected. If the ORG pin is left unconnected, then an internal pull-up device will select the x16 organization.

ORDERING INFORMATION

See detailed ordering and shipping information in the package dimensions section on page 8 of this data sheet.

Table 1. ABSOLUTE MAXIMUM RATINGS

Parameter	Value	Units
Storage Temperature	−65 to +150	°C
Voltage on Any Pin with Respect to Ground (Note 1)	-0.5 to +6.5	V

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality

should not be assumed, damage may occur and reliability may be affected.
1. The DC input voltage on any pin should not be lower than -0.5 V or higher than V_{CC} + 0.5 V. During transitions, the voltage on any pin may undershoot to no less than -1.5 V or overshoot to no more than V_{CC} + 1.5 V, for periods of less than 20 ns.

Table 2. RELIABILITY CHARACTERISTICS (Note 2)

Symbol	Parameter	Min	Units
N _{END} (Note 3)	Endurance	1,000,000 Program	
T _{DR}	Data Retention	100	Years

2. These parameters are tested initially and after a design or process change that affects the parameter according to appropriate AEC-Q100 and JEDEC test methods.

3. Block Mode, V_{CC} = 5 V, T_A = 25^{\circ}C

Table 3. D.C. OPERATING CHARACTERISTICS (V_{CC} = +1.8 V to +5.5 V, unless otherwise specified.)

Symbol	Parameter	Test Conditions	Min	Max	Units
I _{CC1}	Power Supply Current (Write)	f _{SK} = 1 MHz V _{CC} = 5.0 V		1	mA
I _{CC2}	Power Supply Current (Read)	f _{SK} = 1 MHz V _{CC} = 5.0 V		500	μΑ
I _{SB1}	Power Supply Current (Standby) (x8 Mode)	CS = 0 V ORG = GND		10	μΑ
I _{SB2} Power Supply Current (Standby) (x16 Mode)		CS = 0 V ORG = Float or V _{CC}		10	μΑ
Ι _{LI}	Input Leakage Current V _{IN} = 0 V to V _{CC}			2	μA
ILO	Output Leakage Current (Including ORG pin)	$V_{OUT} = 0 V \text{ to } V_{CC},$ CS = 0 V		2	μΑ
V _{IL1}	Input Low Voltage	$4.5 \text{ V} \le \text{V}_{\text{CC}} < 5.5 \text{ V}$	-0.1	0.8	V
V _{IH1}	Input High Voltage	$4.5 \text{ V} \le \text{V}_{\text{CC}} < 5.5 \text{ V}$	2	V _{CC} + 1	V
V _{IL2}	Input Low Voltage	$1.8 \text{ V} \le \text{V}_{\text{CC}} < 4.5 \text{ V}$	0	V _{CC} x 0.2	V
V _{IH2}	Input High Voltage	$1.8 \text{ V} \le \text{V}_{\text{CC}} < 4.5 \text{ V}$	V _{CC} x 0.7	V _{CC} + 1	V
V _{OL1}	Output Low Voltage	$4.5 \text{ V} \le \text{V}_{CC} < 5.5 \text{ V}$ $I_{OL} = 2.1 \text{ mA}$		0.4	V
V _{OH1}	V _{OH1} Output High Voltage 4.5		2.4		V
V _{OL2}	Output Low Voltage	$\begin{array}{l} 1.8 \ V \leq V_{CC} < 4.5 \ V \\ I_{OL} = 1 \ mA \end{array}$		0.2	V
V _{OH2}	Output High Voltage	$\begin{array}{l} 1.8 \ V \leq V_{CC} < 4.5 \ V \\ I_{OH} = -100 \ \mu A \end{array}$	V _{CC} – 0.2		V

Table 4. PIN CAPACITANCE

Symbol	Test	Conditions	Min	Тур	Max	Units
C _{OUT} (Note 4)	Output Capacitance (DO)	V _{OUT} = 0 V			5	pF
C _{IN} (Note 4)	Input Capacitance (CS, SK, DI, ORG)	V _{IN} = 0 V			5	pF

4. These parameters are tested initially and after a design or process change that affects the parameter according to appropriate AEC-Q100 and JEDEC test methods.

Table 5. A.C. CHARACTERISTICS (Note 5)

		V _{CC} = 1.8 V – 5.5 V		V _{CC} = 4.	5 V – 5.5 V		
Symbol	Parameter	Min	Max	Min	Max	Units	
t _{CSS}	CS Setup Time	50		50		ns	
t _{CSH}	CS Hold Time	0		0		ns	
t _{DIS}	DI Setup Time	100		50		ns	
t _{DIH}	DI Hold Time	100		50		ns	
t _{PD1}	Output Delay to 1		0.25		0.1	μs	
t _{PD0}	Output Delay to 0		0.25		0.1	μs	
t _{HZ} (Note 6)	Output Delay to High-Z		100		100	ns	
t _{EW}	Program/Erase Pulse Width		5		5	ms	
t _{CSMIN}	Minimum CS Low Time	0.25		0.1		μs	
t _{SKHI}	Minimum SK High Time	0.25		0.1		μs	
t _{SKLOW}	Minimum SK Low Time	0.25		0.1		μs	
t _{SV}	Output Delay to Status Valid		0.25		0.1	μs	
SK _{MAX}	Maximum Clock Frequency	DC	2	DC	4	MHz	

 Test conditions according to "A.C. Test Conditions" table.
 These parameters are tested initially and after a design or process change that affects the parameter according to appropriate AEC-Q100 and JEDEC test methods.

Table 6. POWER-UP TIMING (Notes 4 and 7)

Symbol	Parameter	Мах	Units
t _{PUR}	Power-up to Read Operation	1	ms
t _{PUW}	Power-up to Write Operation	1	ms

7. t_{PUR} and t_{PUW} are the delays required from the time V_{CC} is stable until the specified operation can be initiated.

Table 7. A.C. TEST CONDITIONS

Input Rise and Fall Times	≤ 50 ns		
Input Pulse Voltages	0.4 V to 2.4 V	$4.5~\textrm{V} \leq \textrm{V}_{\textrm{CC}} \leq 5.5~\textrm{V}$	
Timing Reference Voltages	0.8 V, 2.0 V	$4.5~\textrm{V} \leq \textrm{V}_{\textrm{CC}} \leq 5.5~\textrm{V}$	
Input Pulse Voltages	0.2 V_{CC} to 0.7 V_{CC}	$1.8~\textrm{V} \leq \textrm{V}_{\textrm{CC}} \leq 4.5~\textrm{V}$	
Timing Reference Voltages	0.5 V _{CC}	$1.8~\textrm{V} \leq \textrm{V}_{\textrm{CC}} \leq 4.5~\textrm{V}$	
Output Load	Current Source I _{OLmax} /I _{OHmax} ; C _L = 100 pF		

			Add	ress	Data		
Instruction	Start Bit	Opcode	x8	x16	x8	x16	Comments
READ	1	10	A6-A0	A5-A0			Read Address AN-A0
ERASE	1	11	A6-A0	A5-A0			Clear Address AN–A0
WRITE	1	01	A6-A0	A5-A0	D7-D0	D15-D0	Write Address AN–A0
EWEN	1	00	11XXXXX	11XXXX			Write Enable
EWDS	1	00	00XXXXX	00XXXX			Write Disable
ERAL	1	00	10XXXXX	10XXXX			Clear All Addresses
WRAL	1	00	01XXXXX	01XXXX	D7-D0	D15-D0	Write All Addresses

Table 8. INSTRUCTION SET

Device Operation

The CAT93C46R is a 1024-bit nonvolatile memory intended for use with industry standard microprocessors. The CAT93C46R can be organized as either registers of 16 bits or 8 bits. When organized as X16, seven 9-bit instructions control the reading, writing and erase operations of the device. When organized as X8, seven 10-bit instructions control the reading, writing and erase operations of the device. The CAT93C46R operates on a single power supply and will generate on chip the high voltage required during any write operation.

Instructions, addresses, and write data are clocked into the DI pin on the rising edge of the clock (SK). The DO pin is normally in a high impedance state except when reading data from the device, or when checking the ready/busy status after a write operation.

The ready/busy status can be determined after the start of a write operation by selecting the device (CS high) and polling the DO pin; DO low indicates that the write operation is not completed, while DO high indicates that the device is ready for the next instruction. If necessary, the DO pin may be placed back into a high impedance state during chip select by shifting a dummy "1" into the DI pin. The DO pin will enter the high impedance state on the rising edge of the clock (SK). Placing the DO pin into the high impedance state is recommended in applications where the DI pin and the DO pin are to be tied together to form a common DI/O pin. The Ready/Busy flag can be disabled only in Ready state; no change is allowed in Busy state.

The format for all instructions sent to the device is a logical "1" start bit, a 2-bit (or 4-bit) opcode, 6-bit address (an additional bit when organized X8) and for write operations a 16-bit data field (8-bit for X8 organization).

Read


Upon receiving a READ command and an address (clocked into the DI pin), the DO pin of the CAT93C46R will come out of the high impedance state and, after sending an initial dummy zero bit, will begin shifting out the data addressed (MSB first). The output data bits will toggle on the rising edge of the SK clock and are stable after the specified time delay (t_{PD0} or t_{PD1}).

Sequential Read


After the 1st data word has been shifted out and CS remains asserted with the SK clock continuing to toggle, the CAT93C46R will automatically increment to the next address and shift out the next data word. As long as CS is continuously asserted and SK continues to toggle, the device will keep incrementing to the next address automatically until it reaches the end of the address space, then loops back to address 0. In the sequential Read mode, only the initial data word is preceeded by a dummy zero bit; all subsequent data words will follow without a dummy zero bit.

Erase/Write Enable and Disable

The CAT93C46R powers up in the write disable state. Any writing after power-up or after an EWDS (write disable) instruction must first be preceded by the EWEN (write enable) instruction. Once the write instruction is enabled, it will remain enabled until power to the device is removed, or the EWDS instruction is sent. The EWDS instruction can be used to disable all CAT93C46R write and erase instructions, and will prevent any accidental writing or clearing of the device. Data can be read normally from the device regardless of the write enable/disable status.







Write

After receiving a WRITE command, address and the data, the CS (Chip Select) pin must be deselected for a minimum of t_{CSMIN} (See **Design Note** for details). The falling edge of CS will start the self clocking clear and data store cycle of the memory location specified in the instruction. The clocking of the SK pin is not necessary after the device has entered the self clocking mode. The ready/busy status of the CAT93C46R can be determined by selecting the device and polling the DO pin. Since this device features Auto–Clear before write, it is NOT necessary to erase a memory location before it is written into.

Erase

Upon receiving an ERASE command and address, the CS (Chip Select) pin must be deasserted for a minimum of t_{CSMIN} after the proper number of clock pulses (See **Design Note**). The falling edge of CS will start the self clocking clear cycle of the selected memory location. The clocking of the SK pin is not necessary after the device has entered the self clocking mode. The ready/busy status of the CAT93C46R can be determined by selecting the device and polling the DO pin. Once cleared, the content of a cleared location returns to a logical "1" state.

Erase All

Upon receiving an ERAL command, the CS (Chip Select) pin must be deselected for a minimum of t_{CSMIN}. The falling

edge of CS will start the self clocking clear cycle of all memory locations in the device. The clocking of the SK pin is not necessary after the device has entered the self clocking mode. The ready/busy status of the CAT93C46R can be determined by selecting the device and polling the DO pin. Once cleared, the contents of all memory bits return to a logical "1" state.

Write All

Upon receiving a WRAL command and data, the CS (Chip Select) pin must be deselected for a minimum of t_{CSMIN} . The falling edge of CS will start the self clocking data write to all memory locations in the device. The clocking of the SK pin is not necessary after the device has entered the self clocking mode. The ready/busy status of the CAT93C46R can be determined by selecting the device and polling the DO pin. It is not necessary for all memory locations to be cleared before the WRAL command is executed.

Design Note

With CAT93C46R, after the last data bit has been sampled, Chip Select (CS) must be brought Low before the next rising edge of the clock (SK) in order to start the self-timed high voltage cycle. This is important because if the CS is brought low before or after this specific frame window, the addressed location will not be programmed or erased.





Figure 6. Write Instruction Timing




Ordering Information

OPN	Specific Device Marking	Pkg Type	Temperature Range	Lead Finish	Shipping
CAT93C46RLI-G	93C46RL	PDIP-8	I = Industrial (−40°C to +85°C)	NiPdAu	Tube, 50 Units / Tube
CAT93C46RVI-G	93C46RV	SOIC-8, JEDEC	I = Industrial (−40°C to +85°C)	NiPdAu	Tube, 100 Units / Tube
CAT93C46RVI-GT3	93C46RV	SOIC-8, JEDEC	I = Industrial (−40°C to +85°C)	NiPdAu	Tape & Reel, 3000 Units / Reel
CAT93C46RVP2IGT3 (Note 8)	EL	TDFN-8	I = Industrial (−40°C to +85°C)	NiPdAu	Tape & Reel, 3000 Units / Reel
CAT93C46RYI-G	46R	TSSOP-8	I = Industrial (−40°C to +85°C)	NiPdAu	Tube, 100 Units / Tube
CAT93C46RYI-GT3	46R	TSSOP-8	I = Industrial (−40°C to +85°C)	NiPdAu	Tape & Reel, 3000 Units / Reel

8. Not recommended for new designs.
 9. All packages are RoHS-compliant (Lead-free, Halogen-free).
 10. The standard lead finish is NiPdAu.
 11. For additional package and temperature options, please contact your nearest ON Semiconductor Sales office.
 12. For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.


PACKAGE DIMENSIONS

PDIP-8, 300 mils CASE 646AA-01 **ISSUE A**



SYMBOL	MIN	NOM	MAX		
А			5.33		
A1	0.38				
A2	2.92	3.30	4.95		
b	0.36	0.46	0.56		
b2	1.14	1.52	1.78		
с	0.20	0.25	0.36		
D	9.02	9.27	10.16		
E	7.62	7.87	8.25		
E1	6.10	6.35	7.11		
е	2.54 BSC				
eB	7.87		10.92		
L	2.92	3.30	3.80		


TOP VIEW



SIDE VIEW

Notes:


- All dimensions are in millimeters.
 Complies with JEDEC MS-001.



END VIEW


PACKAGE DIMENSIONS

SOIC 8, 150 mils CASE 751BD-01 ISSUE O



SYMBOL MIN NOM MAX 1.35 А 1.75 0.25 0.10 A1 0.33 0.51 b 0.19 0.25 с D 4.80 5.00 Е 5.80 6.20 E1 3.80 4.00 е 1.27 BSC h 0.25 0.50 0.40 L 1.27 0° 8° θ

TOP VIEW




SIDE VIEW

Notes:

(1) All dimensions are in millimeters. Angles in degrees.


(2) Complies with JEDEC MS-012.



END VIEW


PACKAGE DIMENSIONS

TSSOP8, 4.4x3 CASE 948AL-01 ISSUE O



SYMBOL	MIN	NOM	MAX
А			1.20
A1	0.05		0.15
A2	0.80	0.90	1.05
b	0.19		0.30
с	0.09		0.20
D	2.90	3.00	3.10
E	6.30	6.40	6.50
E1	4.30	4.40	4.50
е	0.65 BSC		
L	1.00 REF		
L1	0.50	0.60	0.75
θ	0°		8°

TOP VIEW



SIDE VIEW




END VIEW

Notes:


All dimensions are in millimeters. Angles in degrees.
 Complies with JEDEC MO-153.

PACKAGE DIMENSIONS

TDFN8, 2x3 CASE 511AK-01 **ISSUE A**







TOP VIEW


SIDE VIEW

BOTTOM VIEW

SYMBOL	MIN	NOM	МАХ
А	0.70	0.75	0.80
A1	0.00	0.02	0.05
A2	0.45	0.55	0.65
A3	0.20 REF		
b	0.20	0.25	0.30
D	1.90	2.00	2.10
D2	1.30	1.40	1.50
E	2.90	3.00	3.10
E2	1.20	1.30	1.40
е	0.50 TYP		
L	0.20	0.30	0.40

Notes:

All dimensions are in millimeters.
 Complies with JEDEC MO-229.



FRONT VIEW

ON Semiconductor and are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at <u>www.onsemi.com/site/pdf/Patent-Marking.pdf</u>. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconducts harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com N. American Technical Support: 800–282–9855 Toll Free USA/Canada Europe, Middle East and Africa Technical Support:

Phone: 421 33 790 2910

ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative