ON Semiconductor

Is Now



To learn more about onsemi™, please visit our website at www.onsemi.com

onsemi and ONSEMI. and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. onsemi reserves the right to make changes at any time to any products or information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/ or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use onsemi products for any such unintended or unauthorized application,



ON Semiconductor®

FDD5N50FTM-WS

N-Channel UniFETTM FRFET[®] MOSFET 500 V, 3.5 A, 1.55 Ω Description

Features

- $R_{DS(on)}$ = 1.25 Ω (Typ.) @ V_{GS} = 10 V, I_D = 1.75 A
- Low Gate Charge (Typ. 11 nC)
- Low C_{rss} (Typ. 5 pF)
- Fast Switching
- · 100% Avalanche Tested
- · Improved dv/dt Capability
- · RoHS Compliant

Applications


- LCD/LED/PDP TV
- Lighting
- · Uninterruptible Power Supply
- AC-DC Power Supply


UniFETTM MOSFET is ON Semiconductor's high voltage MOSFET family based on planar stripe and DMOS technology. This MOSFET is tailored to reduce on-state resistance, and to provide better switching performance and higher avalanche energy strength. The body diode's reverse recovery performance of UniFET FRFET® MOSFET has been enhanced by lifetime control. Its trr is less than 100nsec and the reverse dv/dt immunity is 15V/ns while normal planar MOSFETs have over 200nsec and 4.5V/nsec respectively. Therefore, it can remove additional component and improve system reliability in certain

applications in which the performance of MOSFET's body diode

is significant. This device family is suitable for switching power converter applications such as power factor correction (PFC), flat

panel display (FPD) TV power, ATX and electronic lamp ballasts.





MOSFET Maximum Ratings T_C = 25°C unless otherwise noted.

Symbol		Parameter		Ratings	Units
V_{DSS}	Drain to Source Voltage			500	V
V_{GSS}	Gate to Source Voltage			±30	V
I _D	5 . 6	- Continuous (T _C = 25°C)		3.5	А
	Drain Current	- Continuous (T _C = 100°C)		2.1	A
I _{DM}	Drain Current	- Pulsed	(Note 1)	14	Α
E _{AS}	Single Pulsed Avalanche E	nergy	(Note 2)	257	mJ
I _{AR}	Avalanche Current		(Note 1)	3.5	Α
E _{AR}	Repetitive Avalanche Ener	gy	(Note 1)	4	mJ
dv/dt	Peak Diode Recovery dv/d	t	(Note 3)	4.5	V/ns
В	Dower Discinction	(T _C = 25°C)		40	W
P_{D}	Power Dissipation	- Derate Above 25°C		0.3	W/°C
T _J , T _{STG}	Operating and Storage Ter	nperature Range		-55 to +150	°C
TL	Maximum Lead Temperatu 1/8" from Case for 5 Secon			300	°C

Thermal Characteristics

Symbol	Parameter	Ratings	Units
$R_{\theta JC}$	Thermal Resistance, Junction to Case, Max.	1.4	°C/W
$R_{\theta JA}$	Thermal Resistance, Junction to Ambient, Max.	110	C/VV

Package Marking and Ordering Information

Part Number	Top Mark	Package	Packing Method	Reel Size	Tape Width	Quantity
FDD5N50FTM-WS	FDD5N50F	D-PAK	Tape and Reel	330 mm	16 mm	2500 units

Electrical Characteristics $T_C = 25^{\circ}C$ unless otherwise noted.

Symbol	Parameter	Test Conditions	Min.	Тур.	Max.	Units
Off Charac	cteristics					
BV _{DSS}	Drain to Source Breakdown Voltage	$I_D = 250 \mu A, V_{GS} = 0 V, T_J = 25^{\circ} C$	500	-	-	V
$\frac{\Delta BV_{DSS}}{\Delta T_J}$	Breakdown Voltage Temperature Coefficient	I_D = 250 μ A, Referenced to 25°C	-	0.6	-	V/°C
1	Zero Gate Voltage Drain Current	V _{DS} = 500 V, V _{GS} = 0 V	-	-	10	
IDSS	Zero Gate voltage Drain Current	$V_{DS} = 400 \text{ V}, T_C = 125^{\circ}\text{C}$	_s = 400 V, T _C = 125°C	100	μΑ	
I _{GSS}	Gate to Body Leakage Current	V _{GS} = ±30 V, V _{DS} = 0 V	-	-	±100	nA

On Characteristics

V _{GS(th)}	Gate Threshold Voltage	$V_{GS} = V_{DS}, I_{D} = 250 \mu\text{A}$	3.0	-	5.0	V
R _{DS(on)}	Static Drain to Source On Resistance	V_{GS} = 10 V, I_{D} = 1.75 A	-	1.25	1.55	Ω
9 _{FS}	Forward Transconductance	$V_{DS} = 20 \text{ V}, I_{D} = 1.75 \text{ A}$	-	4.3	ı	S

Dynamic Characteristics

C _{iss}	Input Capacitance		_	490	650	рF
C _{oss}	Output Capacitance	V _{DS} = 25 V, V _{GS} = 0 V f = 1 MHz	-	66	88	pF
C _{rss}	Reverse Transfer Capacitance	1 - 1 1011 12	-	5	7.5	pF
Q _{g(tot)}	Total Gate Charge at 10V		-	11	15	nC
Q_{gs}	Gate to Source Gate Charge	$V_{DS} = 400 \text{ V}, I_{D} = 5 \text{ A},$	-	3	-	nC
Q _{gd}	Gate to Drain "Miller" Charge	V _{GS} = 10 V (Note -	-	5	-	nC

Switching Characteristics

t _{d(on)}	Turn-On Delay Time			-	13	36	ns
t _r	Turn-On Rise Time	V _{DD} = 250 V, I _D = 5 A		-	22	54	ns
t _{d(off)}	Turn-Off Delay Time	$R_G = 25 \Omega$		-	28	66	ns
t _f	Turn-Off Fall Time		(Note 4)	-	20	50	ns

Drain-Source Diode Characteristics

Is	Maximum Continuous Drain to Source Diode Forward Current		-	-	3.5	Α
I _{SM}	Maximum Pulsed Drain to Source Diode Forward Current		-	-	14	Α
V_{SD}	Drain to Source Diode Forward Voltage V _{GS} = 0 V, I _{SD} = 3.5 A		-	-	1.5	V
t _{rr}	Reverse Recovery Time	V _{GS} = 0 V, I _{SD} = 5 A	-	65	-	ns
Q _{rr}	Reverse Recovery Charge	dI _F /dt = 100 A/μs	-	0.120	-	μС

- Notes:
 1: Repetitive rating: pulse-width limited by maximum junction temperature.
 2: L = 42 mH, I_{AS} = 3.5 A, V_{DD} = 50 V, R_G = 25 Ω , starting T_J = 25°C.
 3: I_{SD} < 3.5 A, di/dt < 200 A/µs, V_{DD} \leq BV_{DSS}, starting T_J = 25°C.
 4: Essentially independent of operating temperature typical characteristics.

Typical Performance Characteristics

Figure 1. On-Region Characteristics




Figure 3. On-Resistance Variation vs.

Drain Current and Gate Voltage




Figure 5. Capacitance Characteristics




Figure 2. Transfer Characteristics




Figure 4. Body Diode Forward Voltage Variation vs. Source Current and Temperature





Figure 6. Gate Charge Characteristics



Typical Performance Characteristics (Continued)

Figure 7. Breakdown Voltage Variation vs. Temperature




Figure 9. Maximum Drain Current




Figure 8. Maximum Safe Operating Area





Figure 10. Transient Thermal Response Curve






Figure 11. Gate Charge Test Circuit & Waveform




Figure 12. Resistive Switching Test Circuit & Waveforms





Figure 13. Unclamped Inductive Switching Test Circuit & Waveforms






Figure 14. Peak Diode Recovery dv/dt Test Circuit & Waveforms

ON Semiconductor and in are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hol

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com N. American Technical Support: 800-282-9855 Toll Free USA/Canada Europe, Middle East and Africa Technical Support: Phone: 421 33 790 2910

Phone: 421 33 790 2910

Japan Customer Focus Center
Phone: 81–3–5817–1050

ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative