NSBC123TDP6

Dual NPN Bias Resistor Transistors R1 = 2.2 k Ω , R2 = ∞ k Ω

NPN Transistors with Monolithic Bias Resistor Network

This series of digital transistors is designed to replace a single device and its external resistor bias network. The Bias Resistor Transistor (BRT) contains a single transistor with a monolithic bias network consisting of two resistors; a series base resistor and a base-emitter resistor. The BRT eliminates these individual components by integrating them into a single device. The use of a BRT can reduce both system cost and board space.

Features

- S and NSV Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements; AEC-Q101 Qualified and PPAP Capable
- Simplifies Circuit Design
- Reduces Board Space
- Reduces Component Count
- These Devices are Pb–Free, Halogen Free/BFR Free and are RoHS Compliant

MAXIMUM RATINGS

(T_A = 25°C, common for Q1 and Q2, unless otherwise noted)

Rating	Symbol	Max	Unit
Collector-Base Voltage	V _{CBO}	50	Vdc
Collector-Emitter Voltage	V _{CEO}	50	Vdc
Collector Current – Continuous	۱ _C	100	mAdc
Input Forward Voltage	V _{IN(fwd)}	12	Vdc
Input Reverse Voltage	V _{IN(rev)}	6	Vdc

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

ORDERING INFORMATION

Device	Package	Shipping [†]
NSBC123TDP6T5G	SOT-963	8,000 / Tape & Reel


[†]For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.




ON Semiconductor®

www.onsemi.com

PIN CONNECTIONS



MARKING DIAGRAMS



SOT-963 CASE 527AD

A = M =

Specific Device CodeDate Code*

*Date Code orientation may vary depending upon manufacturing location.

THERMAL CHARACTERISTICS

Characteristic	Symbol	Мах	Unit
ISBC123TDP6 (SOT-963) One Junction Heated			
Total Device Dissipation T _A = 25°C (Note 1) (Note 2) Derate above 25°C (Note 1) (Note 2)	PD	231 269 1.9 2.2	mW mW/°C
Thermal Resistance, (Note 1) Junction to Ambient (Note 2)	R _{0JA}	540 464	°C/W

NSBC123TDP6 (SOT-963) Both Junction Heated (Note 3)

$ \begin{array}{l} \mbox{Total Device Dissipation} \\ T_A = 25^\circ C & (Note 1) \\ (Note 2) \\ \mbox{Derate above } 25^\circ C & (Note 1) \\ (Note 2) \end{array} $	P _D	339 408 2.7 3.3	mW mW/°C
Thermal Resistance,(Note 1)Junction to Ambient(Note 2)	$R_{ hetaJA}$	369 306	°C/W
Junction and Storage Temperature Range	T _J , T _{stg}	–55 to +150	°C


FR-4 @ 100 mm², 1 oz. copper traces, still air.
FR-4 @ 500 mm², 1 oz. copper traces, still air.
Both junction heated values assume total power is sum of two equally powered channels.

NSBC123TDP6

ELECTRICAL CHARACTERISTICS ($T_A = 25^{\circ}C$, common for Q_1 and Q_2 , unless otherwise noted)

Characteristic	Symbol	Min	Тур	Max	Unit
OFF CHARACTERISTICS					
Collector-Base Cutoff Current $(V_{CB} = 50 \text{ V}, I_E = 0)$	I _{CBO}	_	_	100	nAdc
Collector–Emitter Cutoff Current $(V_{CE} = 50 \text{ V}, I_B = 0)$	I _{CEO}	-	_	500	nAdc
Emitter-Base Cutoff Current ($V_{EB} = 6.0 \text{ V}, I_C = 0$)	I _{EBO}	_	-	4.0	mAdc
Collector-Base Breakdown Voltage $(I_C = 10 \ \mu A, I_E = 0)$	V _(BR) CBO	50	_	-	Vdc
Collector–Emitter Breakdown Voltage (Note 4) $(I_C = 2.0 \text{ mA}, I_B = 0)$	V _{(BR)CEO}	50	-	-	Vdc
ON CHARACTERISTICS					
DC Current Gain (Note 4) (I _C = 5.0 mA, V _{CE} = 10 V)	h _{FE}	160	350	-	
Collector–Emitter Saturation Voltage (Note 4) $(I_C = 10 \text{ mA}, I_B = 1.0 \text{ mA})$	V _{CE(sat)}	_	-	0.25	Vdc
Input Voltage (off) (V _{CE} = 5.0 V, I _C = 100 μ A)	V _{i(off)}	-	0.6	-	Vdc
Input Voltage (on) (V _{CE} = 0.2 V, I _C = 10 mA)	V _{i(on)}	_	0.9	-	Vdc
Output Voltage (on) (V _{CC} = 5.0 V, V _B = 2.5 V, R _L = 1.0 k Ω)	V _{OL}	_	_	0.2	Vdc
Output Voltage (off) (V _{CC} = 5.0 V, V _B = 0.25 V, R _L = 1.0 kΩ)	V _{OH}	4.9	_	-	Vdc
Input Resistor	R1	1.5	2.2	2.9	kΩ
Resistor Ratio	R ₁ /R ₂	-	-	_	

4. Pulsed Condition: Pulse Width = 300 msec, Duty Cycle \leq 2%.




(1) SOT-963; 100 mm², 1 oz. copper trace

Figure 1. Derating Curve

NSBC123TDP6

TYPICAL CHARACTERISTICS NSBC123TDP6



MECHANICAL CASE OUTLINE PACKAGE DIMENSIONS



SOT-963 1.00x1.00x0.37, CASE 527AD	0.35P			
ISSUE F			DATE	20 FEB 2024
NDTES:		М	ILLIMETE	RS
1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 2. CONTROLLING DIMENSION: MILLIMETERS.	2018. DIM	MIN.	NDM.	MAX.
3. MAXIMUM LEAD THICKNESS INCLUDES LEAD FINISH THICKNESS. MINIMUM LEAD THICKNESS IS THE MINIM		0,34	0.37	0,40
THICKNESS OF BASE MATERIAL.	h	0.10	0.15	0.20
4. DIMENSIONS D AND E DO NOT INCLUDE MOLD FLASH. PROTRUSIONS, OR GATE BURRS.	,	0.07	0.12	0.17
	D	0.95	1.00	1.05
	E	0,75	0.80	0.85
	e		0.35 BS0	2
+-+-+ Ė ⊢ Ĥ	Н	0.95	1.00	1.05
	L		0.19 REF	-
$T \Pi P V I F W$	L2	0.05	0.10	0.15
	6X 0.20-	┥ 	<u>–6</u>)	K 0.35
				
	, -	┍╘╛╘╈╛╘		
		└── + ─	┦	1.20
			Д	
	INE			
	_	-	0.35 PITCH	
L2→ → ← 6X b (\$\$\0,08 A B]	RECOMME	NDED	MOUNT	ING
	*For addition Free strateg			
STYLE 1: STYLE 2: STYLE 3: PIN 1 EMITTER 1 DIN 1 CATHODE 1	ease download	i the 🛛	1 Semicor	nductor
3. COLLECTOR 2 3. BASE 2 3. ANODE/ANODE 2	Soldering and Reference			
4. EMITTER 2 4. COLLECTOR 2 4. CATHODE 2 5. BASE 2 5. BASE 1 5. CATHODE 2 6. COLLECTOR 1 6. COLLECTOR 1 6. ANODE/ANODE 1				
STYLE 4: STYLE 5: STYLE 6:				
PIN 1. COLLECTOR PIN 1. CATHODE PIN 1. CATHODE 2. COLLECTOR 2. CATHODE 2. ANODE 3. BASE 3. ANODE 3. CATHODE	G	ENERIC		
4. EMITTER4. ANODE4. CATHODE5. COLLECTOR5. CATHODE5. CATHODE		NG DIAGF	RAM*	
6. COLLECTOR 6. CATHODE 6. CATHODE]			
STYLE 7: STYLE 8: STYLE 9: PIN 1. CATHODE PIN 1. DRAIN PIN 1. SOURCE 1 2. ANODE 2. DRAIN 2. GATE 1	1	°XXW		
3. CATHODE 3. GATE 3. DRAIN 2 4. CATHODE 4. SOURCE 4. SOURCE 2	XX - Sn	сific Devic	e Code	
5. ANODE5. DRAIN5. GATE 26. CATHODE6. DRAIN6. DRAIN 1		nth Code		
STYLE 10: PIN 1. CATHODE 1 2. N/C 3. CATHODE 2 4. ANODE 2 5. N/C 6. ANODE 1	*This information device data she Pb-Free indicato or may not be pr not follow the Ge	et for actua or, "G" or m esent. Som	al part marki icrodot "∎", n e products n	ing. nay
	re uncontrolled except when a			
DESCRIPTION: SOT-963 1.00x1.00x0.37, 0.35P			PA	GE 1 OF 1
onsemi and OOSEOD are trademarks of Semiconductor Components Industries LLC dha onsemi or its subsidiaries in the United States and/or other countries onsemi reserves				

onsemi and ONSEMI: are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. onsemi does not convey any license under its patent rights nor the rights of others.

onsemi, ONSEMI, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi's product/patent coverage may be accessed at <u>www.onsemi.com/site/pdf/Patent_Marking.pdf</u>. onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or indental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification. Buyer shall indemnify and hold onsemi and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs,

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:

Technical Library: www.onsemi.com/design/resources/technical-documentation onsemi Website: www.onsemi.com

ONLINE SUPPORT: <u>www.onsemi.com/support</u> For additional information, please contact your local Sales Representative at <u>www.onsemi.com/support/sales</u>