

MOSFET – N-Channel, POWERTRENCH® 150 V, 2 A, 228 mΩ

FDT86246L

General Description

This N-Channel MOSFET is produced using **onsemi**'s advanced POWERTRENCH process that has been optimized for $r_{DS(on)}$, switching performance and ruggedness.

Features

- Max $r_{DS(on)} = 228 \text{ m}\Omega$ at $V_{GS} = 10 \text{ V}$, $I_D = 2 \text{ A}$
- Max $r_{DS(on)} = 280 \text{ m}\Omega$ at $V_{GS} = 4.5 \text{ V}$, $I_D = 1.8 \text{ A}$
- High Performance Trench Technology for Extremely Low r_{DS(on)}
- High Power and Current Handling Capability in a widely used Surface Mount Package
- · Fast Switching Speed
- 100% UIL Tested
- These Devices are Pb-Free and are RoHS Compliant

Applications

- · Load Switch
- Primary Switch
- Buck/Boost Switch


Specifications

MOSFET MAXIMUM RATINGS (T_A = 25°C unless otherwise noted)

Symbol	Parameter		Ratings	Unit
V_{DS}	Drain to Source Voltage		150	V
V_{GS}	Gate to Source Voltage		±20	V
I _D	Drain Current	Continuous T _A = 25°C (Note 1a)	2	Α
		Pulsed (Note 4)	20	
E _{AS}	Single Pulse Avalanche Energy (Note 3)		6	mJ
P _D	Power Dissipation	T _A = 25°C (Note 1a)	2.2	W
		T _A = 25°C (Note 1b)	1.0	
T _J , T _{STG}	Operating and Storage Junction Temperature Range		-55 to +150	°C


Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

1



SOT-223 CASE 318H

MARKING DIAGRAM




A = Assembly Location

Y = Year W = Work Week

6246L = Specific Device Code = Pb-Free Package

(Note: Microdot availability will depend per Assembly site processed. Device is already Pb-free)

PIN ASSIGNMENT



ORDERING INFORMATION


See detailed ordering and shipping information on page 2 of this data sheet.

FDT86246L

THERMAL CHARACTERISTICS

Symbol	Parameter	Ratings	Unit
$R_{ heta JC}$	Thermal Resistance, Junction to Case (Note 1)	12	°C/W
$R_{\theta JA}$	Thermal Resistance, Junction to Ambient (Note 1a)	55	

R_{θJA} is determined with the device mounted on a 1 in² pad 2 oz copper pad on a 1.5 x 1.5 in. board of FR-4 material. R_{θJC} is guaranteed by design while R_{θJA} is determined by the user's board design.



a. 55° C/W when mounted on a 1 in² pad of 2 oz copper



b. 118°C/W when mounted on a minimum pad

ORDERING INFORMATION

Device	Device Marking	Package Type	Shipping [†]
FDT86246L	86246L	SOT-223 (Pb-Free)	4000 units / Tape & Reel

[†]For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

FDT86246L

ELECTRICAL CHARACTERISTICS (T_J = 25°C unless otherwise noted)

Symbol	Parameter	Test Conditions	Min	Тур	Max	Unit
OFF CHARA	ACTERISTICS					
BV _{DSS}	Drain to Source Breakdown Voltage	$I_D = 250 \mu A, V_{GS} = 0 V$	150			V
$\Delta BV_{DSS} / \Delta T_{J}$	Breakdown Voltage Temperature Coefficient	I_D = 250 μ A, referenced to 25°C		110		mV/°C
I _{DSS}	Zero Gate Voltage Drain Current	V _{DS} = 120 V, V _{GS} = 0 V			1	μΑ
I _{GSS}	Gate to Source Leakage Current	V _{GS} = ±20 V, V _{DS} = 0 V			±100	nA
ON CHARA	CTERISTICS					
V _{GS(th)}	Gate to Source Threshold Voltage	$V_{GS} = V_{DS}, I_D = 250 \mu A$	0.8	1.6	2.5	V
$\frac{\Delta V_{GS(th)}}{\Delta T_J}$	Gate to Source Threshold Voltage Temperature Coefficient	I_D = 250 μ A, referenced to 25°C		-5		mV/°C
r _{DS(on)}	Static Drain to Source On Resistance	V _{GS} = 10 V, I _D = 2 A		189	228	mΩ
		V _{GS} = 4.5 V, I _D = 1.8 A		208	280	1
		V _{GS} = 10 V, I _D = 2 A, T _J = 125°C		375	452	1
g _F s	Forward Transconductance	V _{DS} = 10 V, I _D = 2 A		7.3		S
OYNAMIC C	HARACTERISTICS					
C _{iss}	Input Capacitance	V _{DS} = 75 V, V _{GS} = 0 V, f = 1 MHz		238	335	pF
C _{oss}	Output Capacitance	1		20	30	pF
C _{rss}	Reverse Transfer Capacitance	1		2	5	pF
Rg	Gate Resistance		0.1	0.9	2.7	Ω
SWITCHING	CHARACTERISTICS					
t _{d(on)}	Turn-On Delay Time	$V_{DD} = 75 \text{ V}, I_D = 2 \text{ A}, V_{GS} = 10 \text{ V},$		4.5	10	ns
t _r	Rise Time	$R_{GEN} = 6 \Omega$		1.3	10	ns
t _{d(off)}	Turn-Off Delay Time	1		11	20	ns
t _f	Fall Time	1		2	10	ns
Q _{g(TOT)}	Total Gate Charge	V _{GS} = 0 V to 10 V, V _{DD} = 75 V, I _D = 2 A		4.5	6.3	nC
		$V_{GS} = 0 \text{ V to } 4.5 \text{ V}, V_{DD} = 75 \text{ V}, I_D = 2 \text{ A}$		2.3	3.3	nC
Q _{gs}	Gate to Source Charge	V _{DD} = 75 V, I _D = 2 A		0.7		nC
Q _{gd}	Gate to Drain "Miller" Charge	1		1.0		nC
DRAIN-SOL	JRCE DIODE CHARACTERISTICS	•	1			
V _{SD}	Source to Drain Diode Forward Voltage	$V_{GS} = 0 \text{ V, } I_S = 2 \text{ A (Note 2)}$		0.8	1.3	V
t _{rr}	Reverse Recovery Time	I _F = 2 A, di/dt = 100 A/μs		44	71	ns
Q _{rr}	Reverse Recovery Charge	1		31	50	nC

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

- Pulse Test: Pulse Width < 300 µs, Duty cycle < 2.0%.
 E_{AS} of 6 mJ is based on starting T_J = 25°C; N-ch: L = 3 mH, I_{AS} = 2 A, V_{DD} = 150 V, V_{GS} = 10 V. 100% test at L = 0.1 mH, I_{AS} = 7 A.
 Pulsed Id please refer to Figure 11 SOA graph for more details.
- 5. Computed continuous current limited to Max Junction Temperature only, actual continuous current will be limited by thermal & electro-mechanical application board design.

TYPICAL CHARACTERISTICS (T_J = 25°C unless otherwise noted)




Figure 1. On Region Characteristics




Figure 2. Normalized On–Resistance vs.
Drain Current and Gate Voltage




Figure 3. Normalized On Resistance vs. Junction Temperature




Figure 4. On-Resistance vs. Gate to Source Voltage




Figure 5. Transfer Characteristics




Figure 6. Source to Drain Diode Forward Voltage vs. Source Current

TYPICAL CHARACTERISTICS (T_J = 25°C unless otherwise noted) (continued)




Figure 7. Gate Charge Characteristics




Figure 8. Capacitance vs. Drain to Source Voltage




Figure 9. Unclamped Inductive Switching Capability




Figure 10. Forward Bias Safe Operating Area




Figure 11. Single Pulse Maximum Power Dissipation

FDT86246L

TYPICAL CHARACTERISTICS ($T_J = 25$ °C unless otherwise noted) (continued)




Figure 12. Junction-to-Ambient Transient Thermal Response Curve

POWERTRENCH is a registered trademark of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries.

SCALE 2:1



A

В

□ 0.10 M | C | A | B |


DATE 13 MAY 2020


NOTES

- DIMENSIONING AND TOLERANCING PER ASME
- DIMENSIDNING AND TOLERANCING PER ASME
 Y14.5M, 2009.
 CONTROLLING DIMENSION: MILLIMETERS
 DIMENSIONS D & E1 ARE DETERMINED AT DATUM
 H. DIMENSIONS DO NOT INCLUDE MOLD FLASH,
 PROTRUSIONS DR GATE BURRS. SHALL NOT
 EXCEED 0.23mm PER SIDE.
 LEAD DIMENSIONS & AND &1 DO NOT INCLUDE
 DAMBAR PROTRUSION. ALLOWABLE DAMBBAR
 PROTRUSION IS 0.08mm PER SIDE.
 DATUMS A AND B ARE DETERMINED AT DATUM H.
 A1 IS DEFINED AS THE VERTICAL DISTANCE
 FROM THE SEATING PLANE TO THE LOWEST
 POINT OF THE PACKAGE BODY.
 POSITIONAL TOLERANCE APPLIES TO DIMENSIONS
 & AND &1.

- b AND b1.

	MILLIMETERS			
DIM	MIN.	N□M.	MAX.	
Α			1.80	
A1	0.02	0.06	0.11	
b	0.60	0.74	0.88	
b1	2.90	3.00	3.10	
c	0.24		0.35	
D	6.30	6.50	6.70	
E	6.70	7.00	7.30	
E1	3.30	3.50	3.70	
е	2.30 BSC			
L	0.25			
į.	0*		10°	










- = Assembly Location
- = Year
- = Work Week W
- XXXXX = Specific Device Code
- = Pb-Free Package

(Note: Microdot may be in either location)

*This information is generic. Please refer to device data sheet for actual part marking. Pb-Free indicator, "G" or microdot "•", may or may not be present. Some products may not follow the Generic Marking.



RECOMMENDED MOUNTING FOOTPRINT

For additional information on our Pb-Free strategy and soldering details, please download the IN Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

DOCUMENT NUMBER:	98ASH70634A	Electronic versions are uncontrolled except when accessed directly from the Document Repository Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.		
DESCRIPTION:	SOT-223		PAGE 1 OF 1	

ON Semiconductor and unare trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. ON Semiconductor does not convey any license under its patent rights nor the

onsemi, Onsemi, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. Onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA class 3 medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:

 $\textbf{Technical Library:} \ \underline{www.onsemi.com/design/resources/technical-documentation}$

onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support

For additional information, please contact your local Sales Representative at

www.onsemi.com/support/sales